

# EMDR-10 Control Unit



This product is currently being phased out, to be replaced by the all-new Elexant 650c-Modbus. nVent RAYCHEM EMDR-10 is an energy efficient controller for Icestop GM-2X/T self-regulating roof and gutter de-icing systems. Equipped with a temperature and moisture sensor, it only activates the system when detecting cold weather and moisture in combination.

## FEATURES

Simple and fast to install and operate

Energy saving, circuits energized only when cold weather and moisture are detected

Reliable during long life: 6 year product warranty available, maintenance free

## SPECIFICATIONS

Table 1/4

| Catalog Number | Item Name | E-Number   | Voltage Rating | Rated Frequency | Adjustment Range, Frost Protection | Nominal Switching Current @ 250V, Potential Free |
|----------------|-----------|------------|----------------|-----------------|------------------------------------|--------------------------------------------------|
| 449554-000     | EMDR-10   | 9935004156 | 230 V          | 50 Hz min       | -3 to 6 °C                         | 1 A                                              |

Table 2/4

| Catalog Number | Item Name | E-Number   | Sensor Type | Moisture Sensor | Ambient Sensor | Power Consumption, Standby |
|----------------|-----------|------------|-------------|-----------------|----------------|----------------------------|
| 449554-000     | EMDR-10   | 9935004156 | PTC         | Yes             | Yes            | 4 W                        |

Table 3/4

| Catalog Number | Item Name | E-Number | IP Rating | Height | Width | Depth |
|----------------|-----------|----------|-----------|--------|-------|-------|
|----------------|-----------|----------|-----------|--------|-------|-------|

|            |         |            |      |       |        |       |
|------------|---------|------------|------|-------|--------|-------|
| 449554-000 | EMDR-10 | 9935004156 | IP20 | 90 mm | 110 mm | 58 mm |
|------------|---------|------------|------|-------|--------|-------|

Table 4/4

| Catalog Number | Item Name | E-Number   | Shortest Temperature Phase |
|----------------|-----------|------------|----------------------------|
| 449554-000     | EMDR-10   | 9935004156 | 1 min                      |

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

Tel +1.800.545.6258  
Fax +1.800.527.5703  
[thermal.info@nvent.com](mailto:thermal.info@nvent.com)

### Europe, Middle East, Africa

Tel +32.16.213.511  
Fax +32.16.213.604  
[thermal.info@nvent.com](mailto:thermal.info@nvent.com)

### Asia Pacific

Tel +86.21.2412.1688  
Fax +86.21.5426.3167  
[cn.thermal.info@nvent.com](mailto:cn.thermal.info@nvent.com)

### Latin America

Tel +1.713.868.4800  
Fax +1.713.868.2333  
[thermal.info@nvent.com](mailto:thermal.info@nvent.com)

Our powerful portfolio of brands:

**RAYCHEM PYROTENAX TRACER NUHEAT**