


# Novastar Glass Door, 180° Opening Angle

## Power Utilities



Glazed / Glass doors for aluminum frame cabinets with attractive design, ideally suited for general electronics, test & measurement, audio/video and broadcasting applications.

## CERTIFICATIONS



## FEATURES

Glass type: ESG 6 mm, EN 12150

Opening angle 180°

Lock with key

Can be assembled at front and rear

## SPECIFICATIONS

Table 1/2

| Catalog Number | Rack Height | Height  | Width  | Color      | Color Code | Product Type |
|----------------|-------------|---------|--------|------------|------------|--------------|
| 27230-001      | 6 U         | 323 mm  | 553 mm | Light Grey | RAL 7035   | Cabinet Door |
| 27230-002      | 9 U         | 422 mm  | 553 mm | Light Grey | RAL 7035   | Cabinet Door |
| 27230-003      | 12 U        | 555 mm  | 553 mm | Light Grey | RAL 7035   | Cabinet Door |
| 27230-004      | 16 U        | 733 mm  | 553 mm | Light Grey | RAL 7035   | Cabinet Door |
| 27230-005      | 20 U        | 911 mm  | 553 mm | Light Grey | RAL 7035   | Cabinet Door |
| 27230-006      | 25 U        | 1133 mm | 553 mm | Light Grey | RAL 7035   | Cabinet Door |
| 27230-028      | 29 U        | 1345 mm | 553 mm | Light Grey | RAL 7035   | Cabinet Door |
| 27230-007      | 34 U        | 1534 mm | 553 mm | Light Grey | RAL 7035   | Cabinet Door |
| 27230-008      | 38 U        | 1711 mm | 553 mm | Light Grey | RAL 7035   | Cabinet Door |
| 27230-009      | 43 U        | 1933 mm | 553 mm | Light Grey | RAL 7035   | Cabinet Door |
| 27230-010      | 47 U        | 2111 mm | 553 mm | Light Grey | RAL 7035   | Cabinet Door |

Table 2/2

| Catalog Number | Type       |
|----------------|------------|
| 27230-001      | Glass Door |
| 27230-002      | Glass Door |
| 27230-003      | Glass Door |
| 27230-004      | Glass Door |
| 27230-005      | Glass Door |

| Catalog Number | Type       |
|----------------|------------|
| 27230-006      | Glass Door |
| 27230-028      | Glass Door |
| 27230-007      | Glass Door |
| 27230-008      | Glass Door |
| 27230-009      | Glass Door |
| 27230-010      | Glass Door |

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**