


# Insertor/Extractor Handle Type IET, Grey Lever, Black Button, Top, 100 Pieces

## CATALOG NUMBER

**20817-717**



The inserter/extractor handle, type IET in accordance with IEEE 1101.10. 0,1" offset. Two of these handles can overcome a single lever force of 700 N (per pair).

## CERTIFICATIONS



|                                                                     |
|---------------------------------------------------------------------|
| Suitable for insertion and extraction forces up to 700 N (per pair) |
| In accordance with IEEE 1101.10 and IEC 60297-3-102                 |
| A microswitch can be mounted                                        |
| 0.1" offset is used for PSUs with SMD Plus                          |

|                                       |
|---------------------------------------|
| Package Quantity: 100                 |
| Handle Type: IET; Top Front           |
| Flammability Rating: UL® 94V-0        |
| Color: Grey                           |
| Material: Polycarbonate               |
| Product Type: Handle                  |
| Type: Inserter/Extractor, 0.1" Offset |
| Works With: Front Panels              |
| Net Weight: 2.28kg                    |

Please order Coding pegs and Microswitch separately.

[illegible]

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper

installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

**North America**

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

**Europe**

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

**Asia**

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

**Middle East & India**

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**