

2 Hole Lug



FEATURES

Provides an efficient bolting surface for grounding and power applications

Electrolytic grade copper

For use with nVent ERICO Cadweld type LA connections only

SPECIFICATIONS

Material: Copper

Type: NEMA®

Finish: Tinned

Table 1/2

Catalog Number	Length (L)	Width (W)	Thickness (T)	A	B	Hole Size (HS)
B102CE	101.6mm	25.4 mm	3.18 mm	15.9 mm	44.45 mm	14.29 mm
B103CE002	88.9mm	25.4 mm	3.18 mm	15.9 mm	44.45 mm	11.11 mm
B102DE	101.6mm	25.4 mm	4.76 mm	15.9 mm	44.45 mm	14.29 mm
B102EE	104.78mm	25.4 mm	6.35 mm	15.9 mm	44.45 mm	14.29 mm
B102EG	104.78mm	38.1 mm	6.35 mm	15.9 mm	44.45 mm	14.29 mm

CatalogNumber	Length (L)	Width (W)	Thickness (T)	A	B	Hole Size (HS)
B102EH	104.78mm	50.8 mm	6.35 mm	15.9 mm	44.45 mm	14.29 mm
B102EH001	152.4mm	50.8 mm	6.35 mm	15.9 mm	44.45 mm	14.29 mm
B103EK004	76.2mm	76.2 mm	6.35 mm	25.4 mm	44.45 mm	14.29 mm
B102GG	120.65mm	38.1 mm	9.53 mm	15.9 mm	44.45 mm	14.29 mm
B102GH	120.65mm	50.8 mm	9.53 mm	15.9 mm	44.45 mm	14.29 mm
B102JH	133.35mm	50.8 mm	12.7 mm	15.9 mm	44.45 mm	14.29 mm


Table 2/2

Catalog Number	Equivalent Conductor Size
B102CE	80.63mm ²
B103CE002	80.63mm ²
B102DE	120.94mm ²
B102EE	161.26mm ²
B102EG	242mm ²
B102EH	322.51mm ²
B102EH001	322.51mm ²
B103EK004	483.77mm ²
B102GG	362.83mm ²
B102GH	483.77mm ²
B102JH	645.03mm ²

ADDITIONAL PRODUCT DETAILS

For sizes not listed, contact us.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE