

Through Roof Assembly, Air Terminal to In-Line Conductor



CERTIFICATIONS



FEATURES

Allows for lightning protection conductors to be concealed in ceiling or walls

SPECIFICATIONS

Conductor Size, UL: Class 1 - Class 2 (4/0 Max)

Table 1/1

Catalog Number	Material	Connection Material, Air Terminal	Connection Material, In-Line Conductor	Thread Size (TS)	Rod Length (L)	Unit Weight
LPC626A58	Aluminum, Copper, Stainless Steel 18-8 (EN 1.4305)	Aluminum	Copper	5/8" UNC	304.8mm	0.48 kg

CatalogNumber	Material	Connection Material, Air Terminal	Connection Material, In-Line Conductor	Thread Size (TS)	Rod Length (L)	Unit Weight
LPC62658	Copper, Stainless Steel 18-8 (EN 1.4305)	Copper	Copper	5/8" UNC	304.8mm	0.48 kg
LPC62638	Copper, Stainless Steel 18-8 (EN 1.4305)	Copper	Copper	3/8" UNC	304.8mm	0.48 kg
LPC62612	Copper, Stainless Steel 18-8 (EN 1.4305)	Copper	Copper	1/2" UNC	304.8mm	0.48 kg
LPA62612	Aluminum, Stainless Steel 18-8 (EN 1.4305)	Aluminum	Aluminum	1/2" UNC	304.8mm	0.48 kg
LPC626A12	Aluminum, Copper, Stainless Steel 18-8 (EN 1.4305)	Aluminum	Copper	1/2" UNC	304.8mm	0.48 kg

ADDITIONAL PRODUCT DETAILS

Always consult the roof manufacturer or owner for proper flashing materials.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

⚠ WARNING: This product can expose you to chemicals including lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE