


Backplane With Through-Connected Signal Lines

Backplane with Through Connected Signal Lines.



CERTIFICATIONS



FEATURES

Power supply at each connector position (row 1 + 32)

Adaptation fields for power connections on 2-layer backplanes

SPECIFICATIONS

Table 1/2

| Catalog Number | Product Type | Number of Slots | Rack Height | Backplane Type | Slot Width | Connector Type |
|----------------|--------------|-----------------|-------------|-----------------|------------|----------------|
| 23007-010 | Backplane | 10 | 3U | 60 Signal Lines | 4HP | C64F |
| 23007-021 | Backplane | 21 | 3U | 60 Signal Lines | 4HP | C64F |
| 23007-040 | Backplane | 10 | 3U | 60 Signal Lines | 4HP | C96F |
| 23007-051 | Backplane | 21 | 3U | 60 Signal Lines | 4HP | C96F |

| CatalogNumber | Product Type | Number ofSlots | Rack Height | BackplaneType | Slot Width | ConnectorType |
|---------------|--------------|----------------|-------------|-----------------|------------|---------------|
| 23007-081 | Backplane | 21 | 3U | 60 Signal Lines | 4HP | |
| 23007-114 | Backplane | 14 | 3U | 60 Signal Lines | 3HP | C64F |
| 23007-128 | Backplane | 28 | 3U | 60 Signal Lines | 3HP | C64F |
| 23007-158 | Backplane | 28 | 3U | 60 Signal Lines | 3HP | C96F |
| 23007-188 | Backplane | 28 | 3U | 60 Signal Lines | 3HP | |
| 23007-410 | Backplane | 10 | 3U | 90 Signal Lines | 4HP | C96F |
| 23007-421 | Backplane | 21 | 3U | 90 Signal Lines | 4HP | C96F |

Table 2/2

| Catalog Number | Power Connector Type | Package Quantity | Quick Ship |
|----------------|----------------------|------------------|------------|
| 23007-010 | Fastons 6.3 x 0.8 mm | 1 | No |
| 23007-021 | Fastons 6.3 x 0.8 mm | 1 | No |
| 23007-040 | Fastons 6.3 x 0.8 mm | 1 | No |
| 23007-051 | Fastons 6.3 x 0.8 mm | 1 | No |
| 23007-081 | Fastons 6.3 x 0.8 mm | 1 | No |
| 23007-114 | Fastons 6.3 x 0.8 mm | 1 | No |
| 23007-128 | Fastons 6.3 x 0.8 mm | 1 | No |
| 23007-158 | Fastons 6.3 x 0.8 mm | 1 | No |
| 23007-188 | Fastons 6.3 x 0.8 mm | 1 | No |
| 23007-410 | Fastons 6.3 x 0.8 mm | 1 | No |

| Catalog Number | Power Connector Type | Package Quantity | Quick Ship |
|----------------|----------------------|------------------|------------|
| 23007-421 | Fastons 6.3 x 0.8 mm | 1 | No |

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE