

# Mounting Plates Power Distribution, BMP



The steel mounting plate contributes to speeding up the assembly of the terminal box since it can be machined easily and equipped with components before being mounted.

## FEATURES

---

Description: Steel mounting plate for terminal boxes.

Material: 2 mm galvanized steel.

Pack quantity: 1 piece.

## SPECIFICATIONS

**Thickness:** 2mm  
**Finish:** Galvanized  
**Material:** Mild Steel

Table 1/1

| Catalog Number | Height | Width | Depth | Panel Size  | Enclosure Material | Quick Ship |
|----------------|--------|-------|-------|-------------|--------------------|------------|
| BMP1515        | 150mm  | 150mm | 2mm   | 125 x 120mm | Mild Steel         | No         |
| BMP1530        | 150mm  | 300mm | 2mm   | 125 x 270mm | Mild Steel         | No         |
| BMP2020        | 200mm  | 200mm | 2mm   | 175 x 170mm | Mild Steel         | No         |
| BMP2030        | 200mm  | 300mm | 2mm   | 175 x 270mm | Mild Steel         | No         |
| BMP2040        | 200mm  | 400mm | 2mm   | 175 x 370mm | Mild Steel         | No         |
| BMP2050        | 200mm  | 500mm | 2mm   | 175 x 470mm | Mild Steel         | No         |
| BMP2060        | 200mm  | 600mm | 2mm   | 180 x 570mm | Mild Steel         | No         |
| BMP2080        | 200mm  | 800mm | 2mm   | 180 x 770mm | Mild Steel         | No         |
| BMP3030        | 300mm  | 300mm | 2mm   | 275 x 270mm | Mild Steel         | No         |
| BMP3040        | 300mm  | 400mm | 2mm   | 275 x 370mm | Mild Steel         | No         |
| BMP3050        | 300mm  | 500mm | 2mm   | 275 x 470mm | Mild Steel         | No         |
| BMP3060        | 300mm  | 600mm | 2mm   | 280 x 570mm | Mild Steel         | No         |
| BMP4040        | 400mm  | 400mm | 2mm   | 375 x 370mm | Mild Steel         | No         |
| BMP4060        | 400mm  | 600mm | 2mm   | 380 x 570mm | Mild Steel         | No         |
| BMP4080        | 400mm  | 800mm | 2mm   | 380 x 770mm | Mild Steel         | No         |

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper

installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**