

Varistar CP Seismic Base/Plinth

Power Utilities

A plinth allows functional storage of excess cable assemblies and protects the bottom part of the cabinet against rodents.

FEATURES

2 support profiles, St, 10 mm, side

Seismic dynamic load-carrying capacity 500 kg

Height 103 mm

2 covers, St, 10 mm, front and rear

Conforms to NEBS, Earthquake secure (up) to Bellcore Zone 4, tested with 500 KGs, Mounting holes for fitting of base

Access possible from front and rear

SPECIFICATIONS

Table 1/2

Catalog Number	Width	Depth	Color	Color Code	Complies With	Height
21630-115	800 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2	103 mm
21630-114	800 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2	103 mm
21630-110	600 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2	103 mm
21630-113	600 mm	1200 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2	103 mm
21630-117	800 mm	1200 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2	103 mm
21630-112	600 mm	1000 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2	103 mm
21630-111	600 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2	103 mm

CatalogNumber	Width	Depth	Color	Color Code	Complies With	Height
21630-116	800 mm	1000 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2	800 mm

Table 2/2

Catalog Number	Material	Product Type	Static Load	Type	Works With
21630-115	Steel	Cabinet/Rack Base	400 N	Base Plinth	Varistar CP
21630-114	Steel	Cabinet/Rack Base	400 N	Base Plinth	Varistar CP
21630-110	Steel	Cabinet/Rack Base	400 N	Base Plinth	Varistar CP
21630-113	Steel	Cabinet/Rack Base	400 N	Base Plinth	Varistar CP
21630-117	Steel	Cabinet/Rack Base	400 N	Base Plinth	Varistar CP
21630-112	Steel	Cabinet/Rack Base	400 N	Base Plinth	Varistar CP
21630-111	Steel	Cabinet/Rack Base	400 N	Base Plinth	Varistar CP
21630-116	Steel	Cabinet/Rack Base	400 N	Base Plinth	Varistar CP

ADDITIONAL PRODUCT DETAILS

Please purchase the grounding kit separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE