nVent SCHROFF

We connect and protect

Varistar CP Base Plate, Multi-Piece



Multi piece base plate is assembled from inside.

Please order grounding, cover plate, brush strip or filter mat separately.

FEATURES

To cover the base opening

The multi-part base plate is open at the rear (opening to rear 200 mm deep, no rear opening with 300 mm cabinet depth)

SPECIFICATIONS

Product Type: Cabinet/Rack Base

Material: Steel

Table 1/2

Catalog Number	Width	Depth	Package Quantity	Frame	Color	Color Code
21630-616	600mm	600mm	1	Stationary	Black Grey	RAL 7021
21630-617	600mm	800mm	1	Stationary	Black Grey	RAL 7021

CatalogNumber	Width	Depth	Package Quantity	Frame	Color	Color Code
21630-618	600mm	900mm	1	Stationary	Black Grey	RAL 7021
21630-619	600mm	1000mm	1	Stationary	Black Grey	RAL 7021
21630-620	600mm	1100mm	1	Stationary	Black Grey	RAL 7021
21630-621	600mm	1200mm	1	Stationary	Black Grey	RAL 7021
21630-622	800mm	600mm	1	Stationary	Black Grey	RAL 7021
21630-623	800mm	800mm	1	Stationary	Black Grey	RAL 7021
21630-624	800mm	900mm	1	Stationary	Black Grey	RAL 7021
21630-625	800mm	1000mm	1	Stationary	Black Grey	RAL 7021
21630-626	800mm	1100mm	1	Stationary	Black Grey	RAL 7021
21630-627	800mm	1200mm	1	Stationary	Black Grey	RAL 7021
21630-802	600mm	600mm	1	Mobile	Black Grey	RAL 7021
21630-803	600mm	800mm	1	Mobile	Black Grey	RAL 7021
21630-804	600mm	900mm	1	Mobile	Black Grey	RAL 7021
21630-805	600mm	1000mm	1	Mobile	Black Grey	RAL 7021
21630-806	600mm	1100mm	1	Mobile	Black Grey	RAL 7021
21630-807	600mm	1200mm	1	Mobile	Black Grey	RAL 7021
21630-808	800mm	600mm	1	Mobile	Black Grey	RAL 7021
21630-809	800mm	800mm	1	Mobile	Black Grey	RAL 7021

CatalogNumber	Width	Depth	Package Quantity	Frame	Color	Color Code
21630-810	800mm	900mm	1	Mobile	Black Grey	RAL 7021
21630-811	800mm	1000mm	1	Mobile	Black Grey	RAL 7021
21630-812	800mm	1100mm	1	Mobile	Black Grey	RAL 7021
21630-813	800mm	1200mm	1	Mobile	Black Grey	RAL 7021

Table 2/2

Catalog Number	Finish	Quick Ship
21630-616	Powder Coated	No
21630-617	Powder Coated	No
21630-618	Powder Coated	No
21630-619	Powder Coated	No
21630-620	Powder Coated	No
21630-621	Powder Coated	No
21630-622	Powder Coated	No
21630-623	Powder Coated	No
21630-624	Powder Coated	No
21630-625	Powder Coated	No
21630-626	Powder Coated	No
21630-627	Powder Coated	No
21630-802	Powder Coated	No

Catalog Number	Finish	Quick Ship
21630-803	Powder Coated	No
21630-804	Powder Coated	No
21630-805	Powder Coated	No
21630-806	Powder Coated	No
21630-807	Powder Coated	No
21630-808	Powder Coated	No
21630-809	Powder Coated	No
21630-810	Powder Coated	No
21630-811	Powder Coated	No
21630-812	Powder Coated	No
21630-813	Powder Coated	No

ADDITIONAL PRODUCT DETAILS

Multi piece base plate is assembled from inside.

Please order grounding, cover plate, brush strip or filter mat separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America
All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe
Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia
Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India
Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff

Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

©2025 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.