

# 19" Drawer With Keyboard 1 U, Touchpad, RAL 9005

19" rack mountable drawer with keyboard with full extension.



## CERTIFICATIONS



## FEATURES

Extendable 1 U drawer with keyboard including function keys, number pad, touchpad

Locking at full extension and in the inserted state

Connection to USB for keyboard and mouse

Installation dimension 19" rail distance (c-dimension) from 470 ... 700 mm)

Color jet black (RAL 9005)

## SPECIFICATIONS

**Product Type:** Cabinet/Rack Drawer

Table 1/2

| Catalog Number | Rack Height | Depth | Color     | Package Quantity | Color Code | Type     |
|----------------|-------------|-------|-----------|------------------|------------|----------|
| 60118-566      | 1U          | 400mm | Jet Black | 1                | RAL 9005   | Keyboard |

| CatalogNumber | Rack Height | Depth | Color     | Package Quantity | Color Code | Type     |
|---------------|-------------|-------|-----------|------------------|------------|----------|
| 60118-569     | 1U          | 400mm | Jet Black | 1                | RAL 9005   | Keyboard |
| 60118-568     | 1U          | 400mm | Jet Black | 1                | RAL 9005   | Keyboard |
| 60118-567     | 1U          | 400mm | Jet Black | 1                | RAL 9005   | Keyboard |

Table 2/2

| Catalog Number | Works With   | Keyboard Type | Quick Ship |
|----------------|--------------|---------------|------------|
| 60118-566      | 19" Cabinets | QWERTZ        | No         |
| 60118-569      | 19" Cabinets | QWERTY UK     | No         |
| 60118-568      | 19" Cabinets | AZERTY        | No         |
| 60118-567      | 19" Cabinets | QWERTY US     | No         |

## ADDITIONAL PRODUCT DETAILS

Other keyboard layouts, trackball and connections on request.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**