

# MTCA.4 Filler Module Without Air Baffle



To cover unused AdvancedMC, MCH or PM slots in MTCA.1 and MTCA.4 systems or unused slots in a MTCA.0 system with locking bar. Modules consist of a front panel with latches and captive screws, EMC gasket and side panel. Modules can be fixed to the card cage with the captive screws.

## CERTIFICATIONS



## FEATURES

In accordance with MicroTCA.1 and MicroTCA.4 specifications

To cover unused slots within a MicroTCA.1 or MicroTCA.4 System

Flanges with captive M3 screws for fixing to the card cage

EMC shielded

## SPECIFICATIONS

|                        |               |
|------------------------|---------------|
| <b>Type:</b>           | Filler Module |
| <b>Product Family:</b> | MicroTCA      |
| <b>Product Type:</b>   | System Module |

Table 1/1

| Catalog Number | Design Feature | Package Quantity | Material        | Quick Ship |
|----------------|----------------|------------------|-----------------|------------|
| 21850-138      | Mid-Size       | 1                | Stainless Steel | No         |
| 21850-139      | Full-Size      | 1                | Stainless Steel | No         |

| Catalog Number | Design Feature | Package Quantity | Material        | Quick Ship |
|----------------|----------------|------------------|-----------------|------------|
| 21850-140      | Mid-Size       | 1                | Stainless Steel | No         |
| 21850-141      | Full-Size      | 1                | Stainless Steel | No         |

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**