


# PEMSA Wire Basket Tray Rapide

## Data Solutions



The PEMS A Wire Basket Tray is the backbone of PEMS A Wire Basket Tray System. Highly engineered features help ensure a secure installation that complies with industry codes and standards for high-performance cables. Clever design allows the installer to maximize field efficiency with the Rejiband Rapide Integrated Splice.

### CERTIFICATIONS



### FEATURES

Provides optimal support for high-performance low voltage and data cables

Innovative Rejiband Rapide installation system

IEC 61537 load rating and earthing compliant

Responsive design and layout services, including seismic

### SPECIFICATIONS

**Material:** Carbon Steel

**Finish:** Electrogalvanized

Table 1/2

| Catalog Number | Article Number | Length (L) | Height (H) | Width (W) | A | Unit Weight |
|----------------|----------------|------------|------------|-----------|---|-------------|
|----------------|----------------|------------|------------|-----------|---|-------------|

|                   |        |        |       |       |      |        |
|-------------------|--------|--------|-------|-------|------|--------|
| WBT100X100Q<br>BG | 823015 | 3000mm | 100mm | 100mm | 32mm | 3.27kg |
| WBT100X100Q<br>EG | 823014 | 3000mm | 100mm | 100mm | 32mm | 3.27kg |
| WBT100X150Q<br>BG | 823025 | 3000mm | 100mm | 150mm | 32mm | 3.45kg |
| WBT100X150Q<br>EG | 823024 | 3000mm | 100mm | 150mm | 32mm | 3.45kg |
| WBT100X200Q<br>BG | 823035 | 3000mm | 100mm | 200mm | 32mm | 4.14kg |
| WBT100X200Q<br>EG | 823034 | 3000mm | 100mm | 200mm | 32mm | 4.14kg |
| WBT100X300Q<br>BG | 823045 | 3000mm | 100mm | 300mm | 32mm | 6.15kg |
| WBT100X300Q<br>EG | 823044 | 3000mm | 100mm | 300mm | 32mm | 6.15kg |
| WBT100X400Q<br>BG | 823055 | 3000mm | 100mm | 400mm | 32mm | 7.23kg |
| WBT100X400Q<br>EG | 823054 | 3000mm | 100mm | 400mm | 32mm | 7.23kg |
| WBT100X450Q<br>BG | 823085 | 3000mm | 100mm | 450mm | 32mm | 7.44kg |
| WBT100X450Q<br>EG | 823084 | 3000mm | 100mm | 450mm | 32mm | 7.44kg |
| WBT100X500Q<br>BG | 823065 | 3000mm | 100mm | 500mm | 32mm | 8.34kg |
| WBT100X500Q<br>EG | 823064 | 3000mm | 100mm | 500mm | 32mm | 8.34kg |

|                   |        |        |       |       |      |        |
|-------------------|--------|--------|-------|-------|------|--------|
| WBT100X600Q<br>BG | 823075 | 3000mm | 100mm | 600mm | 32mm | 9.42kg |
| WBT100X600Q<br>EG | 823074 | 3000mm | 100mm | 600mm | 32mm | 9.42kg |
| WBT60X100QB<br>G  | 820015 | 3000mm | 60mm  | 100mm | 32mm | 2.43kg |
| WBT60X100QE<br>G  | 820014 | 3000mm | 60mm  | 100mm | 32mm | 2.43kg |
| WBT60X150QB<br>G  | 820025 | 3000mm | 60mm  | 150mm | 32mm | 2.6kg  |
| WBT60X150QE<br>G  | 820024 | 3000mm | 60mm  | 150mm | 32mm | 2.6kg  |
| WBT60X200QB<br>G  | 820035 | 3000mm | 60mm  | 200mm | 32mm | 3.33kg |
| WBT60X200QE<br>G  | 820034 | 3000mm | 60mm  | 200mm | 32mm | 3.33kg |
| WBT60X300QB<br>G  | 820045 | 3000mm | 60mm  | 300mm | 32mm | 5.13kg |
| WBT60X300QE<br>G  | 820044 | 3000mm | 60mm  | 300mm | 32mm | 5.13kg |
| WBT60X400QB<br>G  | 820055 | 3000mm | 60mm  | 400mm | 32mm | 6.21kg |
| WBT60X400QE<br>G  | 820054 | 3000mm | 60mm  | 400mm | 32mm | 6.21kg |
| WBT60X450QB<br>G  | 820085 | 3000mm | 60mm  | 450mm | 32mm | 6.39kg |
| WBT60X450QE<br>G  | 820084 | 3000mm | 60mm  | 450mm | 32mm | 6.39kg |

|                  |        |        |      |       |      |        |
|------------------|--------|--------|------|-------|------|--------|
| WBT60X500QB<br>G | 820065 | 3000mm | 60mm | 500mm | 32mm | 7.35kg |
| WBT60X500QE<br>G | 820064 | 3000mm | 60mm | 500mm | 32mm | 7.35kg |
| WBT60X600QB<br>G | 820079 | 3000mm | 60mm | 600mm | 32mm | 8.43kg |
| WBT60X600QE<br>G | 820078 | 3000mm | 60mm | 600mm | 32mm | 8.43kg |
| WBT60X60QBG      | 820005 | 3000mm | 60mm | 60mm  | 32mm | 2.32kg |


Table 2/2

| Catalog Number | Article Number | Color |
|----------------|----------------|-------|
| WBT100X100QBG  | 823015         | Black |
| WBT100X100QEG  | 823014         | Gray  |
| WBT100X150QBG  | 823025         | Black |
| WBT100X150QEG  | 823024         | Gray  |
| WBT100X200QBG  | 823035         | Black |
| WBT100X200QEG  | 823034         | Gray  |
| WBT100X300QBG  | 823045         | Black |
| WBT100X300QEG  | 823044         | Gray  |
| WBT100X400QBG  | 823055         | Black |
| WBT100X400QEG  | 823054         | Gray  |
| WBT100X450QBG  | 823085         | Black |

| Catalog Number | Article Number | Color |
|----------------|----------------|-------|
| WBT100X450QEG  | 823084         | Gray  |
| WBT100X500QBG  | 823065         | Black |
| WBT100X500QEG  | 823064         | Gray  |
| WBT100X600QBG  | 823075         | Black |
| WBT100X600QEG  | 823074         | Gray  |
| WBT60X100QBG   | 820015         | Black |
| WBT60X100QEG   | 820014         | Gray  |
| WBT60X150QBG   | 820025         | Black |
| WBT60X150QEG   | 820024         | Gray  |
| WBT60X200QBG   | 820035         | Black |
| WBT60X200QEG   | 820034         | Gray  |
| WBT60X300QBG   | 820045         | Black |
| WBT60X300QEG   | 820044         | Gray  |
| WBT60X400QBG   | 820055         | Black |
| WBT60X400QEG   | 820054         | Gray  |
| WBT60X450QBG   | 820085         | Black |
| WBT60X450QEG   | 820084         | Gray  |
| WBT60X500QBG   | 820065         | Black |

| Catalog Number | Article Number | Color |
|----------------|----------------|-------|
| WBT60X500QEG   | 820064         | Gray  |
| WBT60X600QBG   | 820079         | Black |
| WBT60X600QEG   | 820078         | Gray  |
| WBT60X60QBG    | 820005         | Black |

## DIAGRAMS



## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**