

# Mounting Plates Power Distribution, BMP



The steel mounting plate contributes to speeding up the assembly of the terminal box since it can be machined easily and equipped with components before being mounted.

## FEATURES

---

Description: Steel mounting plate for terminal boxes.

Material: 2 mm galvanized steel.

Pack quantity: 1 piece.

## SPECIFICATIONS

**Thickness:** 2mm  
**Finish:** Galvanized  
**Material:** Mild Steel

Table 1/1

Catalog Number	Article Number	Height	Width	Depth	Panel Size	Enclosure Material
BMP1515	BMP1515	150mm	150mm	2mm	125 x 120mm	Mild Steel
BMP1530	BMP1530	150mm	300mm	2mm	125 x 270mm	Mild Steel
BMP2020	BMP2020	200mm	200mm	2mm	175 x 170mm	Mild Steel
BMP2030	BMP2030	200mm	300mm	2mm	175 x 270mm	Mild Steel
BMP2040	BMP2040	200mm	400mm	2mm	175 x 370mm	Mild Steel
BMP2050	BMP2050	200mm	500mm	2mm	175 x 470mm	Mild Steel
BMP2060	BMP2060	200mm	600mm	2mm	180 x 570mm	Mild Steel
BMP2080	BMP2080	200mm	800mm	2mm	180 x 770mm	Mild Steel
BMP3030	BMP3030	300mm	300mm	2mm	275 x 270mm	Mild Steel
BMP3040	BMP3040	300mm	400mm	2mm	275 x 370mm	Mild Steel
BMP3050	BMP3050	300mm	500mm	2mm	275 x 470mm	Mild Steel
BMP3060	BMP3060	300mm	600mm	2mm	280 x 570mm	Mild Steel
BMP4040	BMP4040	400mm	400mm	2mm	375 x 370mm	Mild Steel
BMP4060	BMP4060	400mm	600mm	2mm	380 x 570mm	Mild Steel
BMP4080	BMP4080	400mm	800mm	2mm	380 x 770mm	Mild Steel

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper

installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**