


SBPM/SBPML High Performance Hollow Core Rail Drill Bit, Powder Metal



FEATURES

Designed for high-speed drilling applications

Withstands approximately 100 uses

Drill bits can be reground approximately five times

3/4" (19 mm) Weldon shank

Can be used on all rail types

Specifically developed for rail steel

Allows for short drill times

High durability provides extended lifetime

SPECIFICATIONS

Material: High-Speed Steel

Finish: TIALN Multi-Layer Coating


Table 1/1

Catalog Number	Article Number	Drill Bit Diameter (Ø)	Length (L)
SBPM1270	716473	12"	61mm
SBPM1370	716474	13"	61mm

Catalog Number	Article Number	Drill Bit Diameter (Ø)	Length (L)
SBPM1470	716475	14"	61mm
SBPM1570	716476	15"	61mm
SBPM1870	715274	18"	61mm
SBPM2070	715272	20"	61mm
SBPM2270	715030	22"	61mm
SBPML1990	716310	19"	90mm
SBPML2090	716311	20"	90mm
SBPML2190	716477	21"	90mm
SBPML2290	715280	22"	90mm
SBPML2390	716478	23"	90mm
SBPML2490	716479	24"	90mm
SBPML2590	716480	25"	90mm
SBPML2690	716481	26"	90mm
SBPML2790	716482	27"	90mm
SBPML2890	716483	28"	90mm
SBPML2990	716484	29"	90mm
SBPML3090	716485	30"	90mm
SBPML3190	716486	31"	90mm

Catalog Number	Article Number	Drill Bit Diameter (Ø)	Length (L)
SBPML3290	716487	32"	90mm
SBPML3390	716488	33"	90mm
SBPML3490	716489	34"	90mm
SBPML3590	716490	35"	90mm
SBPML3690	716491	36"	90mm

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE