

# Cable Door Switch for EL LED Enclosure Lights

Ready to use cables for infeed power, through wiring and door switches. The cables are available in different colors.



## FEATURES

---

Description: Pre-fabricated cables for LED enclosure lights. Using these cables will save time and ease mounting of the lights.

Connection: Infeed, with through wiring 3-pole cables (24V is with 2-pole cable).

Dimensions: Different lengths: See article list for more info.

## SPECIFICATIONS

**Material:** Copper

**Finish:** Smooth

Table 1/1

| Catalog Number | Article Number | Product Family          | Color  | Length | Cable Type            | Connection Type                        |
|----------------|----------------|-------------------------|--------|--------|-----------------------|----------------------------------------|
| ELC3001DU      | ELC3001DU      | IEC General Accessories | Black  | 3000mm | Cable for Door Switch | TPS-Cable for Doorswitch, UL Version   |
| ELC1005PB      |                | IEC General Accessories | Black  | 1000mm | Connection Cable      | Infeed, 3 Pole, 100-240 V AC           |
| ELC1005PO      |                | IEC General Accessories | Orange | 1000mm | Connection Cable      | Infeed, 3 Pole, 100-240 V AC           |
| ELC1005TB      |                | IEC General Accessories | Black  | 1000mm | Through Wiring        | Trough-Wiring, 3 Pole, 100-240 V AC    |
| ELC1005TG24V   |                | IEC General Accessories | Gray   | 1000mm | Through Wiring        | Trough-Wiring, 2-Pole, 24 V (DC)       |
| ELC1005TO      |                | IEC General Accessories | Orange | 1000mm | Through Wiring        | Trough-Wiring, 3 Pole, 100-240 V AC    |
| ELC3001DE      |                | IEC General Accessories | Black  | 3000mm | Cable for Door Switch | TPS-Cable for Doorswitch, ENEC Version |
| ELC3005PB      |                | IEC General Accessories | Black  | 3000mm | Connection Cable      | Infeed, 3 Pole, 100-240 V AC           |
| ELC3005PG24V   |                | IEC General Accessories | Gray   | 3000mm | Connection Cable      | Infeed, 2-Pole, 24 V (DC)              |
| ELC3005PO      |                | IEC General Accessories | Orange | 3000mm | Connection Cable      | Infeed, 3 Pole, 100-240 V AC           |

## ADDITIONAL PRODUCT DETAILS

For UL-cables please contact nVent HOFFMAN.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**