

Novastar Cabinet Without Door and Rear Panel

Power Utilities



Aluminum frame cabinets with attractive design, ideally suited for general electronics, test and measurement, audio/video and broadcasting applications.

CERTIFICATIONS



FEATURES

Static load-carrying capacity up to 400 kg (see specification table)

Type of protection IP 20

Cabinet width only 553 mm

Flush cladding parts

All uprights (front and rear) with 19" cut-outs

Colors: RAL 7021 or color combination RAL 7021/ RAL 7035

Bolted, die-cast frame with Al extrusions

Without door and rear panel

SPECIFICATIONS

Table 1/3

Catalog Number	Rack Height	Frame Color	Height	Frame Color Code	Cladding Material	Width
----------------	-------------	-------------	--------	------------------	-------------------	-------

15230-001	9 U	Black Grey	456 mm	RAL 7021	Steel	553 mm
16230-001	9 U	Black Grey	456 mm	RAL 7021	Steel	553 mm
15230-002	12 U	Black Grey	589 mm	RAL 7021	Steel	553 mm
15230-003	12 U	Black Grey	589 mm	RAL 7021	Steel	553 mm
16230-002	12 U	Black Grey	589 mm	RAL 7021	Steel	553 mm
16230-003	12 U	Black Grey	589 mm	RAL 7021	Steel	553 mm
15230-004	16 U	Black Grey	767 mm	RAL 7021	Steel	553 mm
15230-005	16 U	Black Grey	767 mm	RAL 7021	Steel	553 mm
16230-004	16 U	Black Grey	767 mm	RAL 7021	Steel	553 mm
16230-005	16 U	Black Grey	767 mm	RAL 7021	Steel	553 mm
15230-006	20 U	Black Grey	945 mm	RAL 7021	Steel	553 mm
15230-007	20 U	Black Grey	945 mm	RAL 7021	Steel	553 mm
15230-008	20 U	Black Grey	945 mm	RAL 7021	Steel	553 mm
16230-006	20 U	Black Grey	945 mm	RAL 7021	Steel	553 mm
16230-007	20 U	Black Grey	945 mm	RAL 7021	Steel	553 mm
16230-008	20 U	Black Grey	945 mm	RAL 7021	Steel	553 mm
15230-009	25 U	Black Grey	1167 mm	RAL 7021	Steel	553 mm
15230-010	25 U	Black Grey	1167 mm	RAL 7021	Steel	553 mm
16230-009	25 U	Black Grey	1167 mm	RAL 7021	Steel	553 mm

16230-010	25 U	Black Grey	1167 mm	RAL 7021	Steel	553 mm
15230-011	34 U	Black Grey	1567 mm	RAL 7021	Steel	553 mm
15230-012	34 U	Black Grey	1567 mm	RAL 7021	Steel	553 mm
16230-011	34 U	Black Grey	1567 mm	RAL 7021	Steel	553 mm
16230-012	34 U	Black Grey	1567 mm	RAL 7021	Steel	553 mm
15230-013	38 U	Black Grey	1745 mm	RAL 7021	Steel	553 mm
15230-014	38 U	Black Grey	1745 mm	RAL 7021	Steel	553 mm
16230-013	38 U	Black Grey	1745 mm	RAL 7021	Steel	553 mm
16230-014	38 U	Black Grey	1745 mm	RAL 7021	Steel	553 mm
15230-015	43 U	Black Grey	1967 mm	RAL 7021	Steel	553 mm
15230-016	43 U	Black Grey	1967 mm	RAL 7021	Steel	553 mm
16230-015	43 U	Black Grey	1967 mm	RAL 7021	Steel	553 mm
16230-016	43 U	Black Grey	1967 mm	RAL 7021	Steel	553 mm
15230-017	47 U	Black Grey	2145 mm	RAL 7021	Steel	553 mm
15230-018	47 U	Black Grey	2145 mm	RAL 7021	Steel	553 mm
16230-017	47 U	Black Grey	2145 mm	RAL 7021	Steel	553 mm
16230-018	47 U	Black Grey	2145 mm	RAL 7021	Steel	553 mm

Table 2/3						
Catalog Number	Cladding Color	Depth	Static Load	Cladding Color Code	Complies With	Frame Material

15230-001	Black Grey	600 mm	200 kgf	RAL 7021	IEC 60297-3-100	Aluminum
16230-001	Light Grey	600 mm	200 kgf	RAL 7035	IEC 60297-3-100	Aluminum
15230-002	Black Grey	500 mm	200 kgf	RAL 7021	IEC 60297-3-100	Aluminum
15230-003	Black Grey	600 mm	200 kgf	RAL 7021	IEC 60297-3-100	Aluminum
16230-002	Light Grey	500 mm	200 kgf	RAL 7035	IEC 60297-3-100	Aluminum
16230-003	Light Grey	600 mm	200 kgf	RAL 7035	IEC 60297-3-100	Aluminum
15230-004	Black Grey	500 mm	200 kgf	RAL 7021	IEC 60297-3-100	Aluminum
15230-005	Black Grey	600 mm	200 kgf	RAL 7021	IEC 60297-3-100	Aluminum
16230-004	Light Grey	500 mm	200 kgf	RAL 7035	IEC 60297-3-100	Aluminum
16230-005	Light Grey	600 mm	200 kgf	RAL 7035	IEC 60297-3-100	Aluminum
15230-006	Black Grey	500 mm	200 kgf	RAL 7021	IEC 60297-3-100	Aluminum
15230-007	Black Grey	600 mm	200 kgf	RAL 7021	IEC 60297-3-100	Aluminum
15230-008	Black Grey	800 mm	200 kgf	RAL 7021	IEC 60297-3-100	Aluminum
16230-006	Light Grey	500 mm	200 kgf	RAL 7035	IEC 60297-3-100	Aluminum
16230-007	Light Grey	600 mm	200 kgf	RAL 7035	IEC 60297-3-100	Aluminum
16230-008	Light Grey	800 mm	200 kgf	RAL 7035	IEC 60297-3-100	Aluminum
15230-009	Black Grey	600 mm	200 kgf	RAL 7021	IEC 60297-3-100	Aluminum
15230-010	Black Grey	800 mm	200 kgf	RAL 7021	IEC 60297-3-100	Aluminum
16230-009	Light Grey	600 mm	200 kgf	RAL 7035	IEC 60297-3-100	Aluminum

16230-010	Light Grey	800 mm	200 kgf	RAL 7035	IEC 60297-3-100	Aluminum
15230-011	Black Grey	600 mm	400 kgf	RAL 7021	IEC 60297-3-100	Aluminum
15230-012	Black Grey	800 mm	400 kgf	RAL 7021	IEC 60297-3-100	Aluminum
16230-011	Light Grey	600 mm	400 kgf	RAL 7035	IEC 60297-3-100	Aluminum
16230-012	Light Grey	800 mm	400 kgf	RAL 7035	IEC 60297-3-100	Aluminum
15230-013	Black Grey	600 mm	400 kgf	RAL 7021	IEC 60297-3-100	Aluminum
15230-014	Black Grey	800 mm	400 kgf	RAL 7021	IEC 60297-3-100	Aluminum
16230-013	Light Grey	600 mm	400 kgf	RAL 7035	IEC 60297-3-100	Aluminum
16230-014	Light Grey	800 mm	400 kgf	RAL 7035	IEC 60297-3-100	Aluminum
15230-015	Black Grey	600 mm	400 kgf	RAL 7021	IEC 60297-3-100	Aluminum
15230-016	Black Grey	800 mm	400 kgf	RAL 7021	IEC 60297-3-100	Aluminum
16230-015	Light Grey	600 mm	400 kgf	RAL 7035	IEC 60297-3-100	Aluminum
16230-016	Light Grey	800 mm	400 kgf	RAL 7035	IEC 60297-3-100	Aluminum
15230-017	Black Grey	600 mm	400 kgf	RAL 7021	IEC 60297-3-100	Aluminum
15230-018	Black Grey	800 mm	400 kgf	RAL 7021	IEC 60297-3-100	Aluminum
16230-017	Light Grey	600 mm	400 kgf	RAL 7035	IEC 60297-3-100	Aluminum
16230-018	Light Grey	800 mm	400 kgf	RAL 7035	IEC 60297-3-100	Aluminum

Table 3/3

Catalog Number	Product Type
15230-001	Cabinet

Catalog Number	Product Type
16230-001	Cabinet
15230-002	Cabinet
15230-003	Cabinet
16230-002	Cabinet
16230-003	Cabinet
15230-004	Cabinet
15230-005	Cabinet
16230-004	Cabinet
16230-005	Cabinet
15230-006	Cabinet
15230-007	Cabinet
15230-008	Cabinet
16230-006	Cabinet
16230-007	Cabinet
16230-008	Cabinet
15230-009	Cabinet
15230-010	Cabinet
16230-009	Cabinet

Catalog Number	Product Type
16230-010	Cabinet
15230-011	Cabinet
15230-012	Cabinet
16230-011	Cabinet
16230-012	Cabinet
15230-013	Cabinet
15230-014	Cabinet
16230-013	Cabinet
16230-014	Cabinet
15230-015	Cabinet
15230-016	Cabinet
16230-015	Cabinet
16230-016	Cabinet
15230-017	Cabinet
15230-018	Cabinet
16230-017	Cabinet
16230-018	Cabinet

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper

installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE