

Varistar CP Plain Steel Door, Seismic IP55, With Multi-Point Locking

Power Utilities

IP55 Seismic Steel Door with lever handle and multi-Point locking.

FEATURES

Lever handle with push button

Opening angle 180°

Steel door with Multi-Point locking for EMC applications

SPECIFICATIONS

Table 1/3

Catalog Number	Rack Height	Height	Width	Color	Color Code	Complies With
21630-752	33 U	1600 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2, IEC 60529
21630-753	33 U	1600 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2, IEC 60529
21630-754	38 U	600 mm	600 mm	Black Grey	RAL 7021	IEC 61587-2, IEC 61587-2, IEC 60529
21630-755	38 U	1800 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2, IEC 60529
21630-756	42 U	2000 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2, IEC 60529
21630-757	42 U	2000 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2, IEC 60529

CatalogNumber	Rack Height	Height	Width	Color	Color Code	Complies With
21630-758	47 U	2200 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2, IEC 60529
21630-759	47 U	2200 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2, IEC 60529

Table 2/3

Catalog Number	Locking Type	Material	Product Type	Protection Rating	Rack Width	Type
21630-752	4-Point Locking	Steel	Cabinet Door	IP55		Steel Door, Plain
21630-753	4-Point Locking	Steel	Cabinet Door	IP55	800 HP	Steel Door, Plain
21630-754	4-Point Locking	Steel	Cabinet Door	IP55		Steel Door, Plain
21630-755	4-Point Locking	Steel	Cabinet Door	IP55		Steel Door, Plain
21630-756	4-Point Locking	Steel	Cabinet Door	IP55		Steel Door, Plain
21630-757	4-Point Locking	Steel	Cabinet Door	IP55		Steel Door, Plain
21630-758	5-Point Locking	Steel	Cabinet Door	IP55		Steel Door, Plain
21630-759	5-Point Locking	Steel	Cabinet Door	IP55		Steel Door, Plain

Table 3/3

Catalog Number	Works With
21630-752	Varistar CP
21630-753	Varistar CP
21630-754	Varistar CP
21630-755	Varistar CP
21630-756	Varistar CP

Catalog Number	Works With
21630-757	Varistar CP
21630-758	Varistar CP
21630-759	Varistar CP

ADDITIONAL PRODUCT DETAILS

Please purchase the grounding kit separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE