

19" Telescopic Shelf for Varistar, Novastar, Eurorack, 70 kg



Varistar, Novastar and Eurorack 19" Shelf, Stationary with 70 kg load capacity, perforated for ease of assembly.

CERTIFICATIONS



FEATURES

Perforated cut-outs for assembling cable ties

Static load-carrying capacity 70 kg

Incl. telescopic slides

Locking with T-bar lock possible

St, 1.5 mm

Hammer head perforation for assembly with cable ties

SPECIFICATIONS

Product Type: Shelf

Material: Steel

Table 1/2

Catalog Number	Type	Width	Depth	Package Quantity	Color	Color Code
21130-352	Equipment Shelf	600mm	382mm	1	Black Grey	RAL 7021
21130-353	Telescopic Shelf	600mm	482mm	1	Black Grey	RAL 7021
21130-374	Telescopic Shelf	600mm	565mm	1	Black Grey	RAL 7021
21130-354	Telescopic Shelf	600mm	582mm	1	Black Grey	RAL 7021
21130-375	Telescopic Shelf	600mm	677mm	1	Black Grey	RAL 7021
21130-355	Telescopic Shelf	600mm	682mm	1	Black Grey	RAL 7021
21130-357	Telescopic Shelf	553mm	500mm	1	Black Grey	RAL 7021
21130-358	Telescopic Shelf, Reduced Depth	553mm	500mm	1	Black Grey	RAL 7021
21130-372	Telescopic Shelf	600mm	600mm	1	Black Grey	RAL 7021
21130-373	Telescopic Shelf	400mm	477mm	1	Black Grey	RAL 7021
22130-352	Telescopic Shelf	400mm	382mm	1	Light Grey	RAL 7035
22130-353	Telescopic Shelf	400mm	482mm	1	Light Grey	RAL 7035
22130-354	Telescopic Shelf	400mm	582mm	1	Light Grey	RAL 7035
22130-355	Telescopic Shelf	400mm	682mm	1	Light Grey	RAL 7035
22130-372	Telescopic Shelf	600mm	600mm	1	Light Grey	RAL 7035
22130-373	Telescopic Shelf	600mm	477mm	1	Light Grey	RAL 7035
22130-374	Telescopic Shelf	600mm	800mm	1	Black Grey	RAL 7021

CatalogNumber	Type	Width	Depth	Package Quantity	Color	Color Code
22130-375	Telescopic Shelf	600mm	677mm	1	Light Grey	RAL 7035
27230-108	Telescopic Shelf	600mm	582mm	1	Black Grey	RAL 7021
27230-109	Telescopic Shelf	600mm	682mm	1	Black Grey	RAL 7021

Table 2/2			
Catalog Number	Finish	Works With	Quick Ship
21130-352	Powder Coated	Varistar CP	No
21130-353	Powder Coated	Varistar CP	No
21130-374	Powder Coated	Varistar CP	No
21130-354	Powder Coated		No
21130-375	Powder Coated	Varistar CP	No
21130-355	Powder Coated	Varistar CP	No
21130-357	Powder Coated		No
21130-358	Powder Coated		No
21130-372	Powder Coated	Varistar CP	No
21130-373	Powder Coated	Varistar CP	No
22130-352	Powder Coated		No
22130-353	Powder Coated		No
22130-354	Powder Coated		No
22130-355	Powder Coated		No

Catalog Number	Finish	Works With	Quick Ship
22130-372	Powder Coated		No
22130-373	Powder Coated		No
22130-374	Powder Coated		No
22130-375	Powder Coated		No
27230-108	Powder Coated		No
27230-109	Powder Coated		No

ADDITIONAL PRODUCT DETAILS

Mounting bracket for assembly of telescopic slide at frame please order separately.

Please order T-bar lock separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE