

# Backplane With Through-Connected Signal Lines

Backplane with Through Connected Signal Lines.



## CERTIFICATIONS



## FEATURES

Power supply at each connector position (row 1 + 32)

Adaptation fields for power connections on 2-layer backplanes

## SPECIFICATIONS

Table 1/2

| Catalog Number | Product Type | Number of Slots | Rack Height | Backplane Type  | Slot Width | Connector Type |
|----------------|--------------|-----------------|-------------|-----------------|------------|----------------|
| 23007-188      | Backplane    | 28              | 3U          | 60 Signal Lines | 3HP        |                |
| 23007-010      | Backplane    | 10              | 3U          | 60 Signal Lines | 4HP        | C64F           |
| 23007-081      | Backplane    | 21              | 3U          | 60 Signal Lines | 4HP        |                |
| 23007-114      | Backplane    | 14              | 3U          | 60 Signal Lines | 3HP        | C64F           |

| CatalogNumber | Product Type | Number ofSlots | Rack Height | BackplaneType   | Slot Width | ConnectorType |
|---------------|--------------|----------------|-------------|-----------------|------------|---------------|
| 23007-040     | Backplane    | 10             | 3U          | 60 Signal Lines | 4HP        | C96F          |
| 23007-410     | Backplane    | 10             | 3U          | 90 Signal Lines | 4HP        | C96F          |
| 23007-021     | Backplane    | 21             | 3U          | 60 Signal Lines | 4HP        | C64F          |
| 23007-421     | Backplane    | 21             | 3U          | 90 Signal Lines | 4HP        | C96F          |
| 23007-051     | Backplane    | 21             | 3U          | 60 Signal Lines | 4HP        | C96F          |
| 23007-128     | Backplane    | 28             | 3U          | 60 Signal Lines | 3HP        | C64F          |
| 23007-158     | Backplane    | 28             | 3U          | 60 Signal Lines | 3HP        | C96F          |

Table 2/2

| Catalog Number | Power Connector Type | Package Quantity | Quick Ship |
|----------------|----------------------|------------------|------------|
| 23007-188      | Fastons 6.3 x 0.8 mm | 1                | No         |
| 23007-010      | Fastons 6.3 x 0.8 mm | 1                | No         |
| 23007-081      | Fastons 6.3 x 0.8 mm | 1                | No         |
| 23007-114      | Fastons 6.3 x 0.8 mm | 1                | No         |
| 23007-040      | Fastons 6.3 x 0.8 mm | 1                | No         |
| 23007-410      | Fastons 6.3 x 0.8 mm | 1                | No         |
| 23007-021      | Fastons 6.3 x 0.8 mm | 1                | No         |
| 23007-421      | Fastons 6.3 x 0.8 mm | 1                | No         |
| 23007-051      | Fastons 6.3 x 0.8 mm | 1                | No         |
| 23007-128      | Fastons 6.3 x 0.8 mm | 1                | No         |

| Catalog Number | Power Connector Type | Package Quantity | Quick Ship |
|----------------|----------------------|------------------|------------|
| 23007-158      | Fastons 6.3 x 0.8 mm | 1                | No         |

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**