

# BEP Bar End Protector



Bar end protectors are placed onto the ends of threaded reinforcing steel bars. These protective caps help prevent damage to the nVent LENTON threads and help keep dirt and water out of the threads during storage, transportation and installation.

## FEATURES

Easy to install and remove

Color coded for the appropriate reinforcing bar size

## SPECIFICATIONS

Table 1/1

| Catalog Number | Article Number | Rebar Size, Metric | Rebar Size, US | Rebar Size, Canada | Color  |
|----------------|----------------|--------------------|----------------|--------------------|--------|
| EL10BTP        | 370000         | 10 mm              | #3             |                    | Yellow |
| EL12BTP        | 370010         | 12 mm              | #4             | 10M                | Red    |
| EL14BTP        | 370020         | 14 mm              |                |                    | Green  |
| EL16BTP        | 370060         | 16 mm              | #5             | 15M                | Black  |
| EL18BTP        | 370130         | 18 mm              |                |                    | White  |
| EL20BTP        | 370070         | 20 mm              | #6             | 20M                | Yellow |
| EL22BTP        | 370140         | 22 mm              | #7             |                    | Blue   |

| Catalog Number | Article Number | Rebar Size, Metric | Rebar Size, US | Rebar Size, Canada | Color  |
|----------------|----------------|--------------------|----------------|--------------------|--------|
| EL25BTP        | 370080         | 25 mm              | #8             | 25M                | Red    |
| EL28BTP        | 370090         | 28 mm              | #9             | 30M                | Black  |
| EL30BTP        | 370100         | 30 mm              |                |                    | White  |
| EL32BTP        | 370150         | 32 mm              | #10            |                    | Yellow |
| EL34BTP        | 370160         | 34 mm              |                |                    | Red    |
| EL36BTP        | 370110         | 36 mm              | #11            | 35M                | Blue   |
| EL38BTP        | 370170         | 38 mm              | #12            |                    | White  |
| EL40BTP        | 370120         | 40 mm              |                |                    | Green  |
| EL43TBTP       | 370180         | 43 mm              | #14            | 45M                | Red    |
| EL50TBTP       | 370190         | 50 mm              |                |                    | Black  |
| EL57TBTP       | 370200         | 57 mm              | #18            | 55M                | Blue   |

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

#### North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

#### Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

#### Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

#### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

**CADDY**

**ERICO**

**HOFFMAN**

**ILSCO**

**SCHROFF**

**TRACHTE**