


# ATCA Front Panel, Al-Profile, Reinforced With Spring Loading



AdvancedTCA front panel for spring-loaded IEA handle with die-cast end piece.

## CERTIFICATIONS



## FEATURES

Configuration: Front panel with IEA handle (with/without spring loading)

Al extrusion; for mesh EMC sealing

## SPECIFICATIONS

|                 |             |
|-----------------|-------------|
| Depth (D):      | 1mm         |
| Rack Width:     | 6HP         |
| Rack Height:    | 8U          |
| Material:       | Aluminum    |
| Accessory Type: | Front panel |
| Product Type:   | Front Panel |


Table 1/2

| Catalog Number | Package Quantity | Handle Type | Front Finish | Rear Finish | Finish     | Height (H) |
|----------------|------------------|-------------|--------------|-------------|------------|------------|
| 31596-899      | 1                | Plunger     | Raw          | Raw         | Passivated | 323.15mm   |
| 31596-900      | 1                | Lever       | Raw          | Raw         | Passivated | 323.15mm   |

Table 2/2

| Catalog Number | Width (W) | Quick Ship |
|----------------|-----------|------------|
| 31596-899      | 29mm      | No         |
| 31596-900      | 29mm      | No         |

## DIAGRAMS



**WARNING**

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

**North America**

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

**Europe**

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

**Asia**

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

**Middle East & India**

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**