


Eurorack Base/Plinth, Perforated



A plinth allows functional storage of excess cable assemblies and protects the bottom part of the cabinet against rodents.

CERTIFICATIONS



FEATURES

St, 2.5 mm, RAL 7021

Base/plinth, Al diecast

With ventilation openings front and rear

Can be assembled with filter

Height 100 mm

Covers removable from all sides

SPECIFICATIONS

Product Type: Cabinet/Rack Base

Table 1/2

| Catalog Number | Width | Depth | Material | Package Quantity | Color | Color Code |
|----------------|-------|-------|----------|------------------|------------|------------|
| 22117-864 | 600mm | 600mm | Steel | 1 | Black Grey | RAL 7021 |
| 22117-865 | 600mm | 800mm | Steel | 1 | Black Grey | RAL 7021 |
| 22117-866 | 600mm | 900mm | Steel | 1 | Black Grey | RAL 7021 |

| CatalogNumber | Width | Depth | Material | Package Quantity | Color | Color Code |
|---------------|-------|-------|----------|------------------|------------|------------|
| 22117-867 | 800mm | 600mm | Steel | 1 | Black Grey | RAL 7021 |
| 22117-868 | 800mm | 800mm | Steel | 1 | Black Grey | RAL 7021 |

Table 2/2

| Catalog Number | Finish | Type | Quick Ship |
|----------------|---------------|-------------|------------|
| 22117-864 | Powder Coated | Base Plinth | No |
| 22117-865 | Powder Coated | Base Plinth | No |
| 22117-866 | Powder Coated | Base Plinth | No |
| 22117-867 | Powder Coated | Base Plinth | No |
| 22117-868 | Powder Coated | Base Plinth | No |

ADDITIONAL PRODUCT DETAILS

Filter mat (Item 6) not included, please order separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE