

# RayClic Connection Kit



nVent RAYCHEM RayClic connection system is a simple, fast and reliable set of connection kits developed for select nVent RAYCHEM XL-Trace, IceStop and HWAT self-regulating heating cables. No heat guns or wire stripping are needed, because insulation displacement technology is used to make the electrical connection.

## FEATURES

Simple, fast, intuitive connection: no wire stripping or special tools needed

Lower total installed system cost, due to reduced installation time: cold applied, no heat guns or special tools needed

Reliable during long life: 10 year extended product warranty available, maintenance free

Cold applied, no heat guns needed, no special tools

## SPECIFICATIONS

|                                  |              |
|----------------------------------|--------------|
| <b>Current Rating:</b>           | 20 A         |
| <b>Max Exposure Temperature:</b> | 65 °C        |
| <b>Voltage Rating:</b>           | 240 V        |
| <b>Connection Type:</b>          | Cold Applied |
| <b>Color:</b>                    | Grey         |

Table 1/1

| Catalog Number | Item Name     | Model                                 |
|----------------|---------------|---------------------------------------|
| 001013-000     | RAYCLIC-X-02  | X-Branch                              |
| 235422-000     | RAYCLIC-CE-02 | Power Connection to One Heating Cable |
| 364855-000     | RAYCLIC-S-02  | Heating Cable/Heating Cable           |
| 441524-000     | RAYCLIC-T-02  | T-Branch                              |

| Catalog Number | Item Name     | Model                                  |
|----------------|---------------|----------------------------------------|
| 636284-000     | RAYCLIC-PT-02 | Power Connection and T-Branch          |
| 716976-000     | RAYCLIC-PS-02 | Power Connection to Two Heating Cables |

## ADDITIONAL PRODUCT DETAILS

For proper design and installation of a RayClic connection system, use the appropriate product design guide and the installation instructions included with the connection kit.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

Tel +1.800.545.6258  
 Fax +1.800.527.5703  
[thermal.info@nvent.com](mailto:thermal.info@nvent.com)

### Europe, Middle East, Africa

Tel +32.16.213.511  
 Fax +32.16.213.604  
[thermal.info@nvent.com](mailto:thermal.info@nvent.com)

### Asia Pacific

Tel +86.21.2412.1688  
 Fax +86.21.5426.3167  
[cn.thermal.info@nvent.com](mailto:cn.thermal.info@nvent.com)

### Latin America

Tel +1.713.868.4800  
 Fax +1.713.868.2333  
[thermal.info@nvent.com](mailto:thermal.info@nvent.com)

Our powerful portfolio of brands:

**RAYCHEM   PYROTENAX   TRACER   NUHEAT**