

19" Pusher Fan, 2 U, Axial

Fan tray with integrated pusher fan.



CERTIFICATIONS



FEATURES

Contact protection in accordance with DIN EN ISO 13857

Integrated air deflector prevents heat buildup in the assemblies mounted below

Can be adapted to sub racks

Optionally with additional rear fan, 2 U, for active cooling of assemblies beneath the pusher fan

SPECIFICATIONS

Table 1/1

Catalog Number	Input Voltage AC	Input Voltage DC	Package Quantity	Finish	Material	Quick Ship
10713-518	230V		1	Aluminum-Zinc Plated	Steel, Polypropylene	No
10713-520	115V		1	Aluminum-Zinc Plated	Steel, Polypropylene	No
10713-526	230V		1	Aluminum-Zinc Plated	Steel, Polypropylene	No

CatalogNumber	Input Voltage AC	Input Voltage DC	Package Quantity	Finish	Material	Quick Ship
10713-529		24V min	1	Aluminum-Zinc Plated	Steel, Polypropylene	No
10713-534	230V		1	Aluminum-Zinc Plated	Steel, Polypropylene	No
10713-536	115V		1	Aluminum-Zinc Plated	Steel, Polypropylene	No
10713-537		24V min	1	Aluminum-Zinc Plated	Steel, Polypropylene	No
19713-540			1	Aluminum-Zinc Plated	Steel, Polypropylene	No

ADDITIONAL PRODUCT DETAILS

Please order mains cable separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE