

# Varistar CP Deco Frame for 800W Cabinet



The deco frame is a perfect fit for the Varistar CP in 800mm width without a front door. It conceals any cabling on the sides of the cabinet, streamlining cable routing and equipment mounting for a more efficient installation process and simultaneously improving the cabinet's appearance.

## FEATURES

Conceals cabling beside the 19" panel mount, streamlining cable routing and equipment mounting for a more efficient installation process

Provides easier access to the cabinet's internal components with hinged or removable panels, simplifying maintenance or repairs

Imparts improved functionality, appearance, and durability for Varistar CP cabinets without a door

## SPECIFICATIONS

**Product Type:** Cabinet/Rack Frame

**Material:** Steel

Table 1/2

| Catalog Number | Rack Height | Height | Width | Design Feature   | Package Quantity | Color Code |
|----------------|-------------|--------|-------|------------------|------------------|------------|
| 21630-920      | 47U         | 2200mm | 800mm | Swing frame      | 1                | RAL 7021   |
| 21630-926      | 47U         | 2200mm | 800mm | 19" Slide Mounts | 1                | RAL 7021   |
| 21630-918      | 38U         | 1800mm | 800mm | Swing frame      | 1                | RAL 7021   |
| 21630-925      | 42U         | 2000mm | 800mm | 19" Slide Mounts | 1                | RAL 7021   |
| 21630-919      | 42U         | 2000mm | 800mm | Swing frame      | 1                | RAL 7021   |

| CatalogNumber | Rack Height | Height | Width | Design Feature   | Package Quantity | Color Code |
|---------------|-------------|--------|-------|------------------|------------------|------------|
| 21630-924     | 38U         | 1800mm | 800mm | 19" Slide Mounts | 1                | RAL 7021   |

Table 2/2

| Catalog Number | Finish        | Type       | Quick Ship |
|----------------|---------------|------------|------------|
| 21630-920      | Powder Coated | Deco Frame | No         |
| 21630-926      | Powder Coated | Deco Frame | No         |
| 21630-918      | Powder Coated | Deco Frame | No         |
| 21630-925      | Powder Coated | Deco Frame | No         |
| 21630-919      | Powder Coated | Deco Frame | No         |
| 21630-924      | Powder Coated | Deco Frame | No         |

## ADDITIONAL PRODUCT DETAILS

The deco frame provides easier access to the cabinet's internal components with hinged or removable panels, simplifying maintenance or repairs. It's an essential addition to any electronics cabinet without a front door, particularly for Automated Test Equipment, providing improved functionality, appearance, and durability.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**