


# 19" Front Panel With SUB-D Cut-Out



19" Front Panel with SUB-D Cut-Out or FDDI Cut-Out.

## CERTIFICATIONS



## FEATURES

19" Front Panel with Cutout for Sub-D, ST type 3 or FDDI

## SPECIFICATIONS

<b>Depth (D):</b>	2.5mm
<b>Material:</b>	Aluminum
<b>Accessory Type:</b>	Front panel
<b>Product Type:</b>	Front Panel


Table 1/2

Catalog Number	Rack Height	Rack Width	Package Quantity	Front Finish	Rear Finish	Number of Pins
30118-332	3U	4HP	1	Painted	Conductive	(3) 9
30118-334	3U	4HP	1	Painted	Conductive	(1) 25
30118-335	3U	4HP	1	Painted	Conductive	(2) 25
30118-336	3U	4HP	1	Painted	Conductive	(2) 9
30118-338	3U	4HP	1	Painted	Conductive	(1) 9

Table 2/2

Catalog Number	Color Code	Finish	Height (H)	Width (W)	Quick Ship
30118-332	RAL 7035	Powder Coated	128.4mm	19.98mm	No
30118-334	RAL 7035	Powder Coated	128.4mm	19.98mm	No
30118-335	RAL 7035	Powder Coated	128.4mm	19.98mm	No
30118-336	RAL 7035	Powder Coated	128.4mm	19.98mm	No
30118-338	RAL 7035	Powder Coated	128.4mm	19.98mm	No

## DIAGRAMS



## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**