


APO Mounting Plate



APO Mounting Plates allow convenient component mounting inside APO enclosures.

FEATURES

Convenient component mounting inside APO enclosures

Available in three materials, aluminum, steel and non-metallic

SPECIFICATIONS

Table 1/1						
Catalog Number	Article Number	Height	Width	Depth	Material	Finish
BP1207S	BP1207S	229mm	140mm	2mm	Mild Steel	Powder Coated
BP1212S	BP1212S	229mm	229mm	2mm	Mild Steel	Powder Coated
BP1412S	BP1412S	297mm	254mm	2mm	Mild Steel	Powder Coated
BP1912S	BP1912S	414mm	254mm	2mm	Mild Steel	Powder Coated
BP2212S	BP2212S	483mm	254mm	2mm	Mild Steel	Powder Coated
BP2412S	BP2412S	526mm	254mm	2mm	Mild Steel	Powder Coated
BP2414S	BP2414S	526mm	325mm	2mm	Mild Steel	Powder Coated
BP2424S	BP2424S	526mm	556mm	2mm	Mild Steel	Powder Coated
BP706S	BP706S	140mm	140mm	2mm	Mild Steel	Powder Coated
BP1207A	BP1207A	229mm	140mm	2mm	Aluminum	Mill
BP1212A	BP1212A	229mm	229mm	2mm	Aluminum	Mill
BP1412A	BP1412A	297mm	254mm	2mm	Aluminum	Mill
BP1912A	BP1912A	414mm	254mm	2mm	Aluminum	Mill
BP2212A	BP2212A	483mm	254mm	2mm	Aluminum	Mill
BP2412A	BP2412A	526mm	254mm	2mm	Aluminum	Mill
BP2414A	BP2414A	526mm	325mm	2mm	Aluminum	Mill
BP2424A	BP2424A	526mm	556mm	2mm	Aluminum	Mill
BP706A	BP706A	140mm	140mm	2mm	Aluminum	Mill
BP1207N	BP1207N	229mm	140mm	5mm	Non-Metallic	Natural Unfinished

Catalog Number	Article Number	Height	Width	Depth	Material	Finish
BP1212N	BP1212N	229mm	229mm	5mm	Non-Metallic	Natural Unfinished
BP1412N	BP1412N	297mm	254mm	5mm	Non-Metallic	Natural Unfinished
BP1912N	BP1912N	414mm	254mm	5mm	Non-Metallic	Natural Unfinished
BP2212N	BP2212N	483mm	254mm	5mm	Non-Metallic	Natural Unfinished
BP2412N	BP2412N	526mm	254mm	5mm	Non-Metallic	Natural Unfinished
BP2414N	BP2414N	526mm	325mm	5mm	Non-Metallic	Natural Unfinished
BP2424N	BP2424N	526mm	556mm	5mm	Non-Metallic	Natural Unfinished
BP706N	BP706N	140mm	140mm	5mm	Non-Metallic	Natural Unfinished

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE