

# Guide Rail Accessories for Heavy PCBs, Extra Strong

## Power Utilities



This reinforced guide rail for heavy PCBs of the type accessory, forms a reliable interface between the subrack mechanics and the sub-assemblies. The guide rails can additionally be bolted to the horizontal

### CERTIFICATIONS



### FEATURES

For especially heavy PCBs, plug-in units or frame type plug-in units

Mounting, for bolting to type H (heavy) and type R (rugged) horizontal rails only

Aluminium profile

### SPECIFICATIONS

Table 1/2

| Catalog Number | Board Depth | Groove Width | Color | Material | Product Family | Product Type |
|----------------|-------------|--------------|-------|----------|----------------|--------------|
|----------------|-------------|--------------|-------|----------|----------------|--------------|

|           |        |     |        |          |                                                                                                         |            |
|-----------|--------|-----|--------|----------|---------------------------------------------------------------------------------------------------------|------------|
| 34562-884 | 340 mm | 2   | Silver | Aluminum | EuropacPRO,<br>RatiopacPRO,<br>RatiopacPRO<br>AIR,<br>CompacPRO,<br>PropacPRO,<br>MultipacPRO,<br>Inpac | Guide Rail |
| 34562-885 | 400 mm | 2   | Silver | Aluminum | EuropacPRO,<br>RatiopacPRO,<br>RatiopacPRO<br>AIR,<br>CompacPRO,<br>PropacPRO,<br>MultipacPRO,<br>Inpac | Guide Rail |
| 34562-881 | 160 mm | 2   | Silver | Aluminum | EuropacPRO,<br>RatiopacPRO,<br>RatiopacPRO<br>AIR,<br>CompacPRO,<br>PropacPRO,<br>MultipacPRO,<br>Inpac | Guide Rail |
| 34562-883 | 280 mm | 2   | Silver | Aluminum | EuropacPRO,<br>RatiopacPRO,<br>RatiopacPRO<br>AIR,<br>CompacPRO,<br>PropacPRO,<br>MultipacPRO,<br>Inpac | Guide Rail |
| 34562-882 | 220 mm | 2   | Silver | Aluminum | EuropacPRO,<br>RatiopacPRO,<br>RatiopacPRO<br>AIR,<br>CompacPRO,<br>PropacPRO,<br>MultipacPRO,<br>Inpac | Guide Rail |
| 34564-881 | 160 mm | 2.5 | Silver | Aluminum | EuropacPRO,<br>RatiopacPRO,<br>RatiopacPRO<br>AIR,<br>CompacPRO,<br>PropacPRO,<br>MultipacPRO,<br>Inpac | Guide Rail |

|           |        |     |        |          |                                                                                                         |            |
|-----------|--------|-----|--------|----------|---------------------------------------------------------------------------------------------------------|------------|
| 34564-882 | 220 mm | 2.5 | Silver | Aluminum | EuropacPRO,<br>RatiopacPRO,<br>RatiopacPRO<br>AIR,<br>CompacPRO,<br>PropacPRO,<br>MultipacPRO,<br>Inpac | Guide Rail |
| 34564-883 | 280 mm | 2.5 | Silver | Aluminum | EuropacPRO,<br>RatiopacPRO,<br>RatiopacPRO<br>AIR,<br>CompacPRO,<br>PropacPRO,<br>MultipacPRO,<br>Inpac | Guide Rail |
| 34564-884 | 340 mm | 2.5 | Silver | Aluminum | EuropacPRO,<br>RatiopacPRO,<br>RatiopacPRO<br>AIR,<br>CompacPRO,<br>PropacPRO,<br>MultipacPRO,<br>Inpac | Guide Rail |
| 34564-885 | 400 mm | 2.5 | Silver | Aluminum | EuropacPRO,<br>RatiopacPRO,<br>RatiopacPRO<br>AIR,<br>CompacPRO,<br>PropacPRO,<br>MultipacPRO,<br>Inpac | Guide Rail |

Table 2/2

| Catalog Number | Type       | Works With               |
|----------------|------------|--------------------------|
| 34562-884      | Heavy Duty | Subracks, Cases, Chassis |
| 34562-885      | Heavy Duty | Subracks, Cases, Chassis |
| 34562-881      | Heavy Duty | Subracks, Cases, Chassis |
| 34562-883      | Heavy Duty | Subracks, Cases, Chassis |
| 34562-882      | Heavy Duty | Subracks, Cases, Chassis |

| Catalog Number | Type       | Works With               |
|----------------|------------|--------------------------|
| 34564-881      | Heavy Duty | Subracks, Cases, Chassis |
| 34564-882      | Heavy Duty | Subracks, Cases, Chassis |
| 34564-883      | Heavy Duty | Subracks, Cases, Chassis |
| 34564-884      | Heavy Duty | Subracks, Cases, Chassis |
| 34564-885      | Heavy Duty | Subracks, Cases, Chassis |

## ADDITIONAL PRODUCT DETAILS

Delivery is exclusively in standard pack quantity.

Please take into consideration that deliveries may be carried out in the stated SPQs (SPQ, e.g. 5 pieces, 10 pieces, 50 pieces, etc.). Differing order quantities (e.g. 2 pieces) may be changed to the next possible delivery quantity = Standard Pack Quantity.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**