


# Novastar 19" Panel/Slide Mount

## Power Utilities



Novastar 19" Panel/Slide Mount Kit with load capacity of 400 kg, ensures easy fitting of 19" components to depth members.

## CERTIFICATIONS



## FEATURES

For recessed installation of 19" components

For fitting to depth members (25 mm grid)

Load carrying capacity 400 kg

## SPECIFICATIONS

Table 1/2

| Catalog Number | Rack Height | Package Quantity | Color | Color Code | Height | Product Type |
|----------------|-------------|------------------|-------|------------|--------|--------------|
|----------------|-------------|------------------|-------|------------|--------|--------------|

|           |      |   |            |          |            |             |
|-----------|------|---|------------|----------|------------|-------------|
| 27230-172 | 6 U  | 1 | Black Grey | RAL 7021 | 267.1 mm   | Slide Mount |
| 27230-173 | 9 U  | 1 | Black Grey | RAL 7021 | 400.45 mm  | Slide Mount |
| 27230-174 | 12 U | 1 | Black Grey | RAL 7021 | 533.8 mm   | Slide Mount |
| 27230-175 | 16 U | 1 | Black Grey | RAL 7021 | 711.6 mm   | Slide Mount |
| 27230-176 | 20 U | 1 | Black Grey | RAL 7021 | 889.4 mm   | Slide Mount |
| 27230-177 | 25 U | 1 | Black Grey | RAL 7021 | 1111.65 mm | Slide Mount |
| 27230-178 | 34 U | 1 | Black Grey | RAL 7021 | 1511.7 mm  | Slide Mount |
| 27230-179 | 38 U | 1 | Black Grey | RAL 7021 | 1689.5 mm  | Slide Mount |
| 27230-180 | 43 U | 1 | Black Grey | RAL 7021 | 1911.75 mm | Slide Mount |
| 27230-181 | 47 U | 1 | Black Grey | RAL 7021 | 2089.55 mm | Slide Mount |

Table 2/2

| Catalog Number | Package Unit |
|----------------|--------------|
| 27230-172      | Pair         |
| 27230-173      | Pair         |
| 27230-174      | Pair         |
| 27230-175      | Pair         |
| 27230-176      | Pair         |
| 27230-177      | Pair         |
| 27230-178      | Pair         |
| 27230-179      | Pair         |

| Catalog Number | Package Unit |
|----------------|--------------|
| 27230-180      | Pair         |
| 27230-181      | Pair         |

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE