


# Panhead Screw, Torx

## Power Utilities

Panhead screws.



### CERTIFICATIONS



### FEATURES

Panhead screw

### SPECIFICATIONS

Table 1/2

| Catalog Number | Length | Finish        | Package Quantity | Thread Size | Material | Product Family                                                              |
|----------------|--------|---------------|------------------|-------------|----------|-----------------------------------------------------------------------------|
| 24560-148      | 10 mm  | Nickel Plated | 100              | M2.5        | Steel    |                                                                             |
| 24560-147      | 7 mm   | Nickel Plated | 100              | M2.5        | Steel    | EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO |
| 24560-161      | 12 mm  | Nickel Plated | 100              | M2.5        | Steel    |                                                                             |

| CatalogNumber | Length | Finish        | Package Quantity | Thread Size | Material | Product Family                                                              |
|---------------|--------|---------------|------------------|-------------|----------|-----------------------------------------------------------------------------|
| 24560-135     | 6 mm   | Zinc Plated   | 100              | M4          | Steel    | EuropacPRO                                                                  |
| 24571-371     | 14 mm  | Zinc Plated   | 100              | M4          | Steel    | EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO |
| 24571-372     | 10 mm  | Zinc Plated   | 100              | M4          | Steel    | EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO |
| 24560-178     | 6 mm   | Nickel Plated | 100              | M2.5        | Steel    | EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO |
| 24560-162     | 14 mm  | Nickel Plated | 100              | M2.5        | Steel    |                                                                             |
| 24560-163     | 16 mm  | Nickel Plated | 100              | M2.5        | Steel    |                                                                             |

| Table 2/2      |              |               |                                                         |         |
|----------------|--------------|---------------|---------------------------------------------------------|---------|
| Catalog Number | Product Type | Type          | Works With                                              | Torque  |
| 24560-148      | Screw        | Panhead Screw | Backplanes, Test Adapters                               | 0.3 N·m |
| 24560-147      | Screw        | Panhead Screw | Front Panels, Eurorack, Novastar, Varistar, Varistar CP | 0.3 N·m |
| 24560-161      | Screw        | Panhead Screw | Backplanes, Test Adapters                               | 0.3 N·m |
| 24560-135      | Screw        | Panhead Screw | Subracks                                                | 1.3 N·m |
| 24571-371      | Screw        | Panhead Screw | Front Panels, Eurorack, Novastar, Varistar, Varistar CP | 2.4 N·m |

| Catalog Number | Product Type | Type          | Works With                                              | Torque  |
|----------------|--------------|---------------|---------------------------------------------------------|---------|
| 24571-372      | Screw        | Panhead Screw | Front Panels, Eurorack, Novastar, Varistar, Varistar CP | 2.4 N·m |
| 24560-178      | Screw        | Panhead Screw | Front Panels, Eurorack, Novastar, Varistar, Varistar CP |         |
| 24560-162      | Screw        | Panhead Screw | Backplanes, Test Adapters                               |         |
| 24560-163      | Screw        | Panhead Screw | Backplanes, Test Adapters                               |         |

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE