


Horizontal Rail Insulation Strip



Strip enables an insulated mounting of backplanes or metal plates as supports for connectors. Creates standardized mounting depth for plug-in units in the subrack in conjunction with L-ST and H-ST horizontal rails. Suitable for RatiopacPRO/-AIR, Propac Pro, CompacPRO and EuropacPRO/-Rugged.

CERTIFICATIONS



FEATURES

For insulated mounting of backplanes or metal plates as supports for connectors

Creates standardised mounting depth for plug-in units in the subrack in conjunction with L-ST and H-ST horizontal rails

SPECIFICATIONS

Works With:	Subracks; Cases
Product Family:	EuropacPRO; RatiopacPRO; RatiopacPRO AIR; CompacPRO; PropacPRO; Inpac
Product Type:	Insulation Strip
Material:	Polycarbonate

Table 1/1

Catalog Number	Rack Width	Package Quantity	Flammability Rating	Length	Quick Ship
24560-820	20HP	10	UL® 94V-0	101.5mm	No
24560-884	84HP	10	UL® 94V-0	428.64mm	No

Catalog Number	Rack Width	Package Quantity	Flammability Rating	Length	Quick Ship
24560-863	63HP	10	UL® 94V-0	316.88mm	No
24560-842	42HP	10	UL® 94V-0	210.4mm	No
24560-840	40HP	10	UL® 94V-0	205.12mm	No
24560-828	28HP	10	UL® 94V-0	144.2mm	No

ADDITIONAL PRODUCT DETAILS

Please take into consideration that deliveries may be carried out in the stated SPQs (SPQ, e.g. 5 pieces, 10 pieces, 50 pieces, etc.). Differing order quantities (e.g. 2 pieces) may be changed to the next possible delivery quantity = Standard Pack Quantity.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE