

# 19" Drawer



19" Drawers allow mounting of laptops, writing surfaces for easy operations. The SCHROFF 19" drawer has a load capacity of 15 KG, allowing a wide range of products to be assembled into the drawer.

## CERTIFICATIONS



## FEATURES

Static load-carrying capacity 15 kg

Optional writing surface

## SPECIFICATIONS

**Static Load:** 15kg  
**Product Type:** Cabinet/Rack Drawer  
**Material:** Steel

Table 1/2

| Catalog Number | Rack Height | Finish        | Package Quantity | Color      | Color Code | Front Finish |
|----------------|-------------|---------------|------------------|------------|------------|--------------|
| 20110-054      | 1U          | Powder Coated | 1                | Light Grey | RAL 7035   |              |
| 20110-061      | 1U          | Powder Coated | 1                |            |            | Anodized     |
| 20110-180      | 1U          | Powder Coated | 1                | Black Grey | RAL 7021   |              |

| CatalogNumber | Rack Height | Finish        | Package Quantity | Color      | Color Code | Front Finish |
|---------------|-------------|---------------|------------------|------------|------------|--------------|
| 20110-055     | 2U          | Powder Coated | 1                | Light Grey | RAL 7035   |              |
| 20110-056     | 3U          | Powder Coated | 1                | Light Grey | RAL 7035   |              |
| 20110-062     | 2U          | Powder Coated | 1                |            |            | Anodized     |
| 20110-063     | 3U          | Powder Coated | 1                |            |            | Anodized     |
| 20110-181     | 2U          | Powder Coated | 1                | Black Grey | RAL 7021   |              |
| 20110-182     | 3U          | Powder Coated | 1                | Black Grey | RAL 7021   |              |

Table 2/2

| Catalog Number | Type   | Works With   | Quick Ship |
|----------------|--------|--------------|------------|
| 20110-054      | Drawer | 19" Cabinets | No         |
| 20110-061      | Drawer | 19" Cabinets | No         |
| 20110-180      | Drawer | 19" Cabinets | No         |
| 20110-055      | Drawer | 19" Cabinets | No         |
| 20110-056      | Drawer | 19" Cabinets | No         |
| 20110-062      | Drawer | 19" Cabinets | No         |
| 20110-063      | Drawer | 19" Cabinets | No         |
| 20110-181      | Drawer | 19" Cabinets | No         |
| 20110-182      | Drawer | 19" Cabinets | No         |

## ADDITIONAL PRODUCT DETAILS

Please order 19" assembly kit separately.

**WARNING**

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

**North America**

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

**Europe**

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

**Asia**

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

**Middle East & India**

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**