

# Varistar CP Seismic Base/Plinth

## Power Utilities

A plinth allows functional storage of excess cable assemblies and protects the bottom part of the cabinet against rodents.

### FEATURES

2 support profiles, St, 10 mm, side

Seismic dynamic load-carrying capacity 500 kg

Height 103 mm

2 covers, St, 10 mm, front and rear

Conforms to NEBS, Earthquake secure (up) to Bellcore Zone 4, tested with 500 KGs, Mounting holes for fitting of base

Access possible from front and rear

### SPECIFICATIONS

Table 1/2

| Catalog Number | Width  | Depth   | Color      | Color Code | Complies With               | Height |
|----------------|--------|---------|------------|------------|-----------------------------|--------|
| 21630-110      | 600 mm | 600 mm  | Black Grey | RAL 7021   | IEC 61587-1,<br>IEC 61587-2 | 103 mm |
| 21630-111      | 600 mm | 800 mm  | Black Grey | RAL 7021   | IEC 61587-1,<br>IEC 61587-2 | 103 mm |
| 21630-112      | 600 mm | 1000 mm | Black Grey | RAL 7021   | IEC 61587-1,<br>IEC 61587-2 | 103 mm |
| 21630-113      | 600 mm | 1200 mm | Black Grey | RAL 7021   | IEC 61587-1,<br>IEC 61587-2 | 103 mm |
| 21630-114      | 800 mm | 600 mm  | Black Grey | RAL 7021   | IEC 61587-1,<br>IEC 61587-2 | 103 mm |
| 21630-115      | 800 mm | 800 mm  | Black Grey | RAL 7021   | IEC 61587-1,<br>IEC 61587-2 | 103 mm |
| 21630-117      | 800 mm | 1200 mm | Black Grey | RAL 7021   | IEC 61587-1,<br>IEC 61587-2 | 103 mm |

| CatalogNumber | Width  | Depth   | Color      | Color Code | Complies With               | Height |
|---------------|--------|---------|------------|------------|-----------------------------|--------|
| 21630-116     | 800 mm | 1000 mm | Black Grey | RAL 7021   | IEC 61587-1,<br>IEC 61587-2 | 800 mm |

Table 2/2

| Catalog Number | Material | Product Type      | Static Load | Type        | Works With  |
|----------------|----------|-------------------|-------------|-------------|-------------|
| 21630-110      | Steel    | Cabinet/Rack Base | 400 N       | Base Plinth | Varistar CP |
| 21630-111      | Steel    | Cabinet/Rack Base | 400 N       | Base Plinth | Varistar CP |
| 21630-112      | Steel    | Cabinet/Rack Base | 400 N       | Base Plinth | Varistar CP |
| 21630-113      | Steel    | Cabinet/Rack Base | 400 N       | Base Plinth | Varistar CP |
| 21630-114      | Steel    | Cabinet/Rack Base | 400 N       | Base Plinth | Varistar CP |
| 21630-115      | Steel    | Cabinet/Rack Base | 400 N       | Base Plinth | Varistar CP |
| 21630-117      | Steel    | Cabinet/Rack Base | 400 N       | Base Plinth | Varistar CP |
| 21630-116      | Steel    | Cabinet/Rack Base | 400 N       | Base Plinth | Varistar CP |

## ADDITIONAL PRODUCT DETAILS

Please purchase the grounding kit separately.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**