

Novastar Base Plate, Multi Pieces, Open at Rear



Base plate is a plain steel blanking plate fitted to the cabinet base. Restricts air-flow into the cabinet from floor cavity and can be opened for cable ducting.

CERTIFICATIONS



FEATURES

Base is open at rear for cable ducting; opening can be closed with a plain or perforated cover, filter plate or brush strip

Rear opening, width 440 mm, depth 70 mm

SPECIFICATIONS

Product Type: Cabinet/Rack Base

Material: Steel

Table 1/2

Catalog Number	Width	Depth	Package Quantity	Color	Color Code	Finish
----------------	-------	-------	------------------	-------	------------	--------

27230-188	553mm	500mm	1	Black Grey	RAL 7021	Powder Coated
27230-189	553mm	600mm	1	Black Grey	RAL 7021	Powder Coated
27230-190	553mm	800mm	1	Black Grey	RAL 7021	Powder Coated
27230-191	553mm	900mm	1	Black Grey	RAL 7021	Powder Coated
27230-192	553mm	1000mm	1	Black Grey	RAL 7021	Powder Coated

Table 2/2

Catalog Number	Type	Quick Ship
27230-188	Base Plate	No
27230-189	Base Plate	No
27230-190	Base Plate	No
27230-191	Base Plate	No
27230-192	Base Plate	No

ADDITIONAL PRODUCT DETAILS

Please order cover plate or brush strip separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE