


# Varistar CP Raised Top Cover

Fan top cover for better ventilation and active cooling.



## FEATURES

Uses same lifting eyes as normal top cover

## SPECIFICATIONS

**Product Type:** Cabinet/Rack Top Cover  
**Protection Rating:** IP20  
**Material:** Steel

Table 1/2

Catalog Number	Width	Depth	Package Quantity	Color	Color Code	Finish
21630-583	600mm	300mm	1	Black Grey	RAL 7021	Powder Coated
21630-584	600mm	600mm	1	Black Grey	RAL 7021	Powder Coated
21630-585	600mm	800mm	1	Black Grey	RAL 7021	Powder Coated
21630-586	600mm	900mm	1	Black Grey	RAL 7021	Powder Coated
21630-587	600mm	1000mm	1	Black Grey	RAL 7021	Powder Coated
21630-588	600mm	1100mm	1	Black Grey	RAL 7021	Powder Coated

CatalogNumber	Width	Depth	Package Quantity	Color	Color Code	Finish
21630-589	600mm	1200mm	1	Black Grey	RAL 7021	Powder Coated
21630-590	800mm	600mm	1	Black Grey	RAL 7021	Powder Coated
21630-591	800mm	800mm	1	Black Grey	RAL 7021	Powder Coated
21630-592	800mm	900mm	1	Black Grey	RAL 7021	Powder Coated
21630-593	800mm	1000mm	1	Black Grey	RAL 7021	Powder Coated
21630-594	800mm	1100mm	1	Black Grey	RAL 7021	Powder Coated
21630-595	800mm	1200mm	1	Black Grey	RAL 7021	Powder Coated

Table 2/2

Catalog Number	Quick Ship
21630-583	No
21630-584	No
21630-585	No
21630-586	No
21630-587	No
21630-588	No
21630-589	No
21630-590	No
21630-591	No
21630-592	No

Catalog Number	Quick Ship
21630-593	No
21630-594	No
21630-595	No

## ADDITIONAL PRODUCT DETAILS

Please purchase the grounding kit separately.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**