

# Varistar CP Perforated, Seismic Base Plate, EMC, for Rear Cable Ducting

## Power Utilities

Varistar CP Base Plate for Rear Cable Ducting, plain for IP 55 or EMC applications.

### FEATURES

Installation from outside

Cutout at rear

60 mm deep

Cable ducting with IP 55 / EMC gasket

### SPECIFICATIONS

Table 1/2

| Catalog Number | Width  | Depth   | Color      | Color Code | Complies With                               | Material |
|----------------|--------|---------|------------|------------|---------------------------------------------|----------|
| 20630-325      | 600 mm | 600 mm  | Black Grey | RAL 7021   | IEC 61587-1,<br>IEC 61587-2,<br>IEC 61587-3 | Steel    |
| 20630-326      | 600 mm | 800 mm  | Black Grey | RAL 7021   | IEC 61587-1,<br>IEC 61587-2,<br>IEC 61587-3 | Steel    |
| 20630-327      | 600 mm | 1000 mm | Black Grey | RAL 7021   | IEC 61587-1,<br>IEC 61587-2,<br>IEC 61587-3 | Steel    |
| 20630-328      | 600 mm | 1200 mm | Black Grey | RAL 7021   | IEC 61587-1,<br>IEC 61587-2,<br>IEC 61587-3 | Steel    |
| 20630-329      | 800 mm | 600 mm  | Black Grey | RAL 7021   | IEC 61587-1,<br>IEC 61587-2,<br>IEC 61587-3 | Steel    |
| 20630-330      | 800 mm | 800 mm  | Black Grey | RAL 7021   | IEC 61587-1,<br>IEC 61587-2,<br>IEC 61587-3 | Steel    |

| CatalogNumber | Width  | Depth   | Color      | Color Code | Complies With                               | Material |
|---------------|--------|---------|------------|------------|---------------------------------------------|----------|
| 20630-331     | 800 mm | 1000 mm | Black Grey | RAL 7021   | IEC 61587-1,<br>IEC 61587-2,<br>IEC 61587-3 | Steel    |
| 20630-332     | 800 mm | 1200 mm | Black Grey | RAL 7021   | IEC 61587-1,<br>IEC 61587-2,<br>IEC 61587-3 | Steel    |

Table 2/2

| Catalog Number | Product Type      | Type                   | Works With  |
|----------------|-------------------|------------------------|-------------|
| 20630-325      | Cabinet/Rack Base | Base Plate, Perforated | Varistar CP |
| 20630-326      | Cabinet/Rack Base | Base Plate, Perforated | Varistar CP |
| 20630-327      | Cabinet/Rack Base | Base Plate, Perforated | Varistar CP |
| 20630-328      | Cabinet/Rack Base | Base Plate, Perforated | Varistar CP |
| 20630-329      | Cabinet/Rack Base | Base Plate, Perforated | Varistar CP |
| 20630-330      | Cabinet/Rack Base | Base Plate, Perforated | Varistar CP |
| 20630-331      | Cabinet/Rack Base | Base Plate, Perforated | Varistar CP |
| 20630-332      | Cabinet/Rack Base | Base Plate, Perforated | Varistar CP |

## ADDITIONAL PRODUCT DETAILS

Varistar CP Base Plate for Rear Cable Ducting, plain for IP 55 or EMC applications.

Please purchase the grounding kit separately.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**