

Easy Swap Adaptor Plenums for Air Conditioners



When existing air conditioners are damaged or have reached end-of-life, Easy Swap Adaptor Plenums provide a quick and easy means for attaching a new nVent HOFFMAN air conditioners to the cutout left on the enclosure.

INDUSTRY STANDARDS

Maintains NEMA Type 12 rating when properly installed on a Type 12 enclosure.

NEMA Type 12

IP 54

FEATURES

No modification of the enclosure required - designed to match the enclosure cut-out and mounting holes of the air conditioner being replaced

Plenum design allows for optimum air flow (vs. a flat plate that can block the air intake and air outtake left by the older air conditioner)

Gasket included

SPECIFICATIONS

Color: Light Gray

Color Code: RAL 7035

Table 1/1

Catalog Number	Article Number	Height	Width	Depth	Material	Finish
PL17N21		530mm	305mm	38mm	Mild Steel	Powder Coated
PL17N21SS		530mm	305mm	38mm	Stainless Steel 316L	Brushed #4
PLCR23N21		584mm	254mm	38mm	Mild Steel	Powder Coated
PLCR23N21SS		584mm	254mm	38mm	Stainless Steel 316L	Brushed #4
PLHC52G57	26301	1463mm	583mm	38mm	Mild Steel	Powder Coated
PLHC52T53	26302	1342mm	584mm	38mm	Mild Steel	Powder Coated
PLKG28	26582	937mm	486mm	38mm	Mild Steel	Powder Coated
PLKG52	26581	1335mm	486mm	38mm	Mild Steel	Powder Coated
PLKTN17	26568	483mm	305mm	38mm	Mild Steel	Powder Coated
PLKTN28	26505	845mm	311mm	38mm	Mild Steel	Powder Coated
PLM13N16		448mm	362mm	67mm	Mild Steel	Powder Coated
PLM13N17	26556	448mm	362mm	38mm	Mild Steel	Powder Coated
PLM28G28	26294	724mm	432mm	38mm	Mild Steel	Powder Coated
PLM28N17	26557	724mm	432mm	38mm	Mild Steel	Powder Coated
PLM33N28	26296	871mm	305mm	38mm	Mild Steel	Powder Coated
PLM36N36	26297	984mm	381mm	38mm	Mild Steel	Powder Coated
PLM52G52	26298	1335mm	433mm	38mm	Mild Steel	Powder Coated

Catalog Number	Article Number	Height	Width	Depth	Material	Finish
PLPN36	26537	927mm	305mm	38mm	Mild Steel	Powder Coated
PLR1N17	26066	550mm	330mm	38mm	Mild Steel	Powder Coated
PLR2G28	26504	950mm	431mm	38mm	Mild Steel	Powder Coated
PLR2N17	26067	550mm	305mm	38mm	Mild Steel	Powder Coated
PLRG28	21496	950mm	431mm	38mm	Mild Steel	Powder Coated
PLRG52	19862	1553mm	435mm	38mm	Mild Steel	Powder Coated
PLRG57	26073	1553mm	530mm	38mm	Mild Steel	Powder Coated
PLRN28	26068	737mm	292mm	38mm	Mild Steel	Powder Coated
PLRN36	26538	965mm	400mm	38mm	Mild Steel	Powder Coated
PLT29G28	26295	724mm	432mm	38mm	Mild Steel	Powder Coated

ADDITIONAL PRODUCT DETAILS

To quickly identify the correct air conditioner and plenum download the spec sheet from the Downloads tab or download the Easy Swap app from Apple App or Google play stores

Please contact Customer Service for support in finding an appropriate cross for older HOFFMAN/Mclean models not shown above.

Prior to ordering, ensure Adaptor Plenum dimensions do not exceed available space on the enclosure mounting surface.

ISC is a registered trademark of ISC Sales, Inc.

Kooltronic is a registered trademark of Kooltronic, Inc.

Pfannenbergl is a registered trademark of Pfannenbergl Incorporated

Rittal is a registered trademark of Rittal Corporation

Adaptor Plenums for Rittal are not suitable for replacing partial-recessed or fully-recessed mounted air conditioners.

Thermal Edge is a registered trademark of Thermal Edge, Inc.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause

product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE