

# Gasket Kit



Gasket kits are ideal to replace damaged or worn foam-in-place or strip enclosure gaskets. Available in either EPDM or silicone material, these gasket kits allows replacement of current gasket as well as provides a solution to upgrade enclosure gasket for harsh applications. Kits offered with different sized gaskets is suitable to be used on either Wall-Mount or Free-Stand/Floor-Mount Enclosures.

## INDUSTRY STANDARDS

UL 508A Component Recognized; Type 4, 4x, 12; File No. E61997

cUL Component Recognized per CSA C22.2 No 94; File No. E61997

Suitable for field installation for door, cover and gland plate sealing on HOFFMAN enclosure models rated Types 4, 4X and 12.

## FEATURES

Positioned inside enclosure door providing a sealing barrier between the housing and door of an enclosure

EPDM gasket kits are ideal to replace damaged or worn enclosure gasket

Silicone gasket provides a secure sealing to protect against water and dust ingress in extreme temperatures

Silicone gaskets can be used to upgrade current gasket for harsh applications or ideal to replace current silicone gasket

Strip gasket is field-installable with included sealant and instructions

Gaskets available in .63-in. (16-mm) wide for Wall-Mount Enclosures

Gaskets available in 1.00-in. (25-mm) wide for Free-Stand and Floor-Mount Enclosures

Each kit includes a 20-ft. (6m) roll of strip gasket

SPECIFICATIONS

| Table 1/1      |                |        |       |          |              |       |
|----------------|----------------|--------|-------|----------|--------------|-------|
| Catalog Number | Article Number | Length | Width | Material | Finish       | Color |
| GSKTKITE025    | 29151          | 6.1m   | 16mm  | EPDM     | Smooth Matte | Black |
| GSKTKITS025    | 29153          | 6.1m   | 12mm  | Silicone | Smooth Matte | Black |
| GSKTKITS375    | 29154          | 6.1m   | 25mm  | Silicone | Smooth Matte | Black |
| GSKTKITE375    | 29152          | 6.1m   | 25mm  | EPDM     | Smooth Matte | Black |

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE