

# Varistar CP Seismic Depth Member, 3 Rows, Aluzinc

Horizontal depth member in the cabinet depth. Mounted directly at the Varistar CP frame for cable management, increased frame stiffness and additional fixing points.



## FEATURES

Cable routing facilitated using cable ties and cable eyes, required for recessed shelf

St, 2 mm, finish AlZn

## SPECIFICATIONS

**Finish:** Aluminum-Zinc Plated

**Product Type:** Bracket

**Material:** Steel

Table 1/1

| Catalog Number | Depth  | Package Quantity | Complies With            | Works With  | Quick Ship |
|----------------|--------|------------------|--------------------------|-------------|------------|
| 24630-110      | 600mm  | 1                | IEC 61587-1, IEC 61587-2 | Varistar CP | No         |
| 24630-115      | 1200mm | 1                | IEC 61587-1, IEC 61587-2 | Varistar CP | No         |
| 24630-114      | 1100mm | 1                | IEC 61587-1, IEC 61587-2 | Varistar CP | No         |
| 24630-113      | 1000mm | 1                | IEC 61587-1, IEC 61587-2 | Varistar CP | No         |
| 24630-112      | 900mm  | 1                | IEC 61587-1, IEC 61587-2 | Varistar CP | No         |

| Catalog Number | Depth | Package Quantity | Complies With            | Works With  | Quick Ship |
|----------------|-------|------------------|--------------------------|-------------|------------|
| 24630-111      | 800mm | 1                | IEC 61587-1, IEC 61587-2 | Varistar CP | No         |

## ADDITIONAL PRODUCT DETAILS

Please purchase the grounding kit separately.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**