

# 19" Front Panel With Holes for Handles

## Data Solutions



Define the device fronts and side inss with Schroff 19" front panels. Schroff 19" front panels have additional holes for mounting of handles and are available in 1 U to 6 U demensions.

### CERTIFICATIONS



### FEATURES

19" front panels have additional holes for mounting of handles

### SPECIFICATIONS

|                        |             |
|------------------------|-------------|
| <b>Rack Width:</b>     | 95HP        |
| <b>Material:</b>       | Aluminum    |
| <b>Accessory Type:</b> | Front panel |
| <b>Product Type:</b>   | Front Panel |

Table 1/3

| Catalog Number | Rack Height | Depth (D) | Handle Type  | Finish   | Mounting       | Package Quantity |
|----------------|-------------|-----------|--------------|----------|----------------|------------------|
| 30219-161      | 1U          | 3mm       | Front Handle | Anodized | Screw-on Front | 1                |

| CatalogNumber | Rack Height | Depth (D) | Handle Type  | Finish   | Mounting       | Package Quantity |
|---------------|-------------|-----------|--------------|----------|----------------|------------------|
| 40304-050     | 1U          | 3mm       | Front Handle | Anodized | Screw-on Front | 1                |
| 30219-162     | 2U          | 3mm       | Front Handle | Anodized | Screw-on Front | 1                |
| 40304-051     | 2U          | 3mm       | Front Handle | Anodized | Screw-on Front | 1                |
| 30219-163     | 3U          | 3mm       | Front Handle | Anodized | Screw-on Front | 1                |
| 30219-164     | 4U          | 3mm       | Front Handle | Anodized | Screw-on Front | 1                |
| 40304-052     | 3U          | 3mm       | Front Handle | Anodized | Screw-on Front | 1                |
| 30219-165     | 5U          | 3mm       | Front Handle | Anodized | Screw-on Front | 1                |
| 40304-053     | 4U          | 3mm       | Front Handle | Anodized | Screw-on Front | 1                |
| 30219-166     | 6U          |           | Front Handle | Anodized | Screw-on Front | 1                |
| 40304-054     | 5U          | 3mm       | Front Handle | Anodized | Screw-on Front | 1                |
| 40304-055     | 6U          | 3mm       | Front Handle | Anodized | Screw-on Front | 1                |

| Table 2/3      |              |             |               |               |            |                 |
|----------------|--------------|-------------|---------------|---------------|------------|-----------------|
| Catalog Number | Front Finish | Rear Finish | Treated Edges | EMC Shielding | Height (H) | Type            |
| 30219-161      | Anodized     | Anodized    | No            | No            | 43.6mm     | 19" Front Panel |
| 40304-050      | Anodized     | Anodized    | Yes           | No            | 43.6mm     | 19" Front Panel |
| 30219-162      | Anodized     | Anodized    | No            | No            | 88.1mm     | 19" Front Panel |
| 40304-051      | Anodized     | Anodized    | Yes           | No            | 88.1mm     | 19" Front Panel |
| 30219-163      | Anodized     | Anodized    | No            | No            | 132.5mm    | 19" Front Panel |

| CatalogNumber | Front Finish | Rear Finish | Treated Edges | EMC Shielding | Height (H) | Type            |
|---------------|--------------|-------------|---------------|---------------|------------|-----------------|
| 30219-164     | Anodized     | Anodized    | No            | No            | 177mm      | 19" Front Panel |
| 40304-052     | Anodized     | Anodized    | Yes           | No            | 132.5mm    | 19" Front Panel |
| 30219-165     | Anodized     | Anodized    | No            | No            | 221.4mm    | 19" Front Panel |
| 40304-053     | Anodized     | Anodized    | Yes           | No            | 177mm      | 19" Front Panel |
| 30219-166     | Anodized     | Anodized    | No            | No            | 265.9mm    | 19" Front Panel |
| 40304-054     | Anodized     | Anodized    | Yes           | No            | 221.4mm    | 19" Front Panel |
| 40304-055     | Anodized     | Anodized    | Yes           | No            | 265.9mm    | 19" Front Panel |

Table 3/3

| Catalog Number | Width (W) |
|----------------|-----------|
| 30219-161      | 483mm     |
| 40304-050      | 483mm     |
| 30219-162      | 483mm     |
| 40304-051      | 483mm     |
| 30219-163      | 483mm     |
| 30219-164      | 483mm     |
| 40304-052      | 483mm     |
| 30219-165      | 483mm     |
| 40304-053      | 483mm     |
| 30219-166      | 483mm     |

