


# Combined Mounting Kit for Chassis

## Power Utilities



The combined mounting enable the option to split a 6 U high subrack or case in 2 x 3 U and 6 U sections. Different versions are available.

## CERTIFICATIONS



## FEATURES

Designed to accept Euroboards (100 mm high) and double Euroboards (233.35 mm high)

Subdivision of the 6 U assembly area into: 2 x 3 U, 1 x 6 U

## SPECIFICATIONS

Table 1/2

| Catalog Number | Package Quantity | Rack Width 1 | Rack Width 2 | Product Family | Product Type | Rack Height |
|----------------|------------------|--------------|--------------|----------------|--------------|-------------|
| 24562-484      | 1                | 84 HP        |              | EuropacPRO     | Mounting Kit | 6 U         |
| 24562-420      | 1                | 20 HP        | 62 HP        | EuropacPRO     | Mounting Kit | 6 U         |
| 24562-440      | 1                | 40 HP        | 42 HP        | EuropacPRO     | Mounting Kit | 6 U         |
| 24562-442      | 1                | 42 HP        | 40 HP        | EuropacPRO     | Mounting Kit | 6 U         |

| CatalogNumber | Package Quantity | Rack Width 1 | Rack Width 2 | Product Family | Product Type | Rack Height |
|---------------|------------------|--------------|--------------|----------------|--------------|-------------|
| 24562-463     | 1                | 63 HP        | 19 HP        | EuropacPRO     | Mounting Kit | 6 U         |

Table 2/2

| Catalog Number | Type     | Works With |
|----------------|----------|------------|
| 24562-484      | Combined | Subracks   |
| 24562-420      | Combined | Subracks   |
| 24562-440      | Combined | Subracks   |
| 24562-442      | Combined | Subracks   |
| 24562-463      | Combined | Subracks   |

## ADDITIONAL PRODUCT DETAILS

Please order separately: Front panel 6 U, 2 HP to cover the strut.

The following guide rails cannot be used: type "accessory", type "accessory, strengthened" and type "for 4.4" PCB".

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**