


# PEMSA Wire Basket Tray Rapide



The PEMS A Wire Basket Tray is the backbone of PEMS A Wire Basket Tray System. Highly engineered features help ensure a secure installation that complies with industry codes and standards for high-performance cables. Clever design allows the installer to maximize field efficiency with the Rejiband Rapide Integrated Splice.

## CERTIFICATIONS



## FEATURES

Provides optimal support for high-performance low voltage and data cables

Innovative Rejiband Rapide installation system

IEC 61537 load rating and earthing compliant

Responsive design and layout services, including seismic

## SPECIFICATIONS

**Material:** Carbon Steel

**Finish:** Electrogalvanized

Table 1/2

| Catalog Number    | Article Number | Length (L) | Height (H) | Width (W) | A     | Unit Weight |
|-------------------|----------------|------------|------------|-----------|-------|-------------|
| WBT100X100Q<br>BG | 823015         | 3000mm     | 100 mm     | 100 mm    | 32 mm | 3.27 kg     |

| CatalogNumber     | Article Number | Length (L) | Height (H) | Width (W) | A     | Unit Weight |
|-------------------|----------------|------------|------------|-----------|-------|-------------|
| WBT100X100Q<br>EG | 823014         | 3000mm     | 100 mm     | 100 mm    | 32 mm | 3.27 kg     |
| WBT100X150Q<br>BG | 823025         | 3000mm     | 100 mm     | 150 mm    | 32 mm | 3.45 kg     |
| WBT100X150Q<br>EG | 823024         | 3000mm     | 100 mm     | 150 mm    | 32 mm | 3.45 kg     |
| WBT100X200Q<br>BG | 823035         | 3000mm     | 100 mm     | 200 mm    | 32 mm | 4.14 kg     |
| WBT100X200Q<br>EG | 823034         | 3000mm     | 100 mm     | 200 mm    | 32 mm | 4.14 kg     |
| WBT100X300Q<br>BG | 823045         | 3000mm     | 100 mm     | 300 mm    | 32 mm | 6.15 kg     |
| WBT100X300Q<br>EG | 823044         | 3000mm     | 100 mm     | 300 mm    | 32 mm | 6.15 kg     |
| WBT100X400Q<br>BG | 823055         | 3000mm     | 100 mm     | 400 mm    | 32 mm | 7.23 kg     |
| WBT100X400Q<br>EG | 823054         | 3000mm     | 100 mm     | 400 mm    | 32 mm | 7.23 kg     |
| WBT100X450Q<br>BG | 823085         | 3000mm     | 100 mm     | 450 mm    | 32 mm | 7.44 kg     |
| WBT100X450Q<br>EG | 823084         | 3000mm     | 100 mm     | 450 mm    | 32 mm | 7.44 kg     |
| WBT100X500Q<br>BG | 823065         | 3000mm     | 100 mm     | 500 mm    | 32 mm | 8.34 kg     |
| WBT100X500Q<br>EG | 823064         | 3000mm     | 100 mm     | 500 mm    | 32 mm | 8.34 kg     |

| CatalogNumber     | Article Number | Length (L) | Height (H) | Width (W) | A     | Unit Weight |
|-------------------|----------------|------------|------------|-----------|-------|-------------|
| WBT100X600Q<br>BG | 823075         | 3000mm     | 100 mm     | 600 mm    | 32 mm | 9.42 kg     |
| WBT100X600Q<br>EG | 823074         | 3000mm     | 100 mm     | 600 mm    | 32 mm | 9.42 kg     |
| WBT60X100QB<br>G  | 820015         | 3000mm     | 60 mm      | 100 mm    | 32 mm | 2.43 kg     |
| WBT60X100QE<br>G  | 820014         | 3000mm     | 60 mm      | 100 mm    | 32 mm | 2.43 kg     |
| WBT60X150QB<br>G  | 820025         | 3000mm     | 60 mm      | 150 mm    | 32 mm | 2.6 kg      |
| WBT60X150QE<br>G  | 820024         | 3000mm     | 60 mm      | 150 mm    | 32 mm | 2.6 kg      |
| WBT60X200QB<br>G  | 820035         | 3000mm     | 60 mm      | 200 mm    | 32 mm | 3.33 kg     |
| WBT60X200QE<br>G  | 820034         | 3000mm     | 60 mm      | 200 mm    | 32 mm | 3.33 kg     |
| WBT60X300QB<br>G  | 820045         | 3000mm     | 60 mm      | 300 mm    | 32 mm | 5.13 kg     |
| WBT60X300QE<br>G  | 820044         | 3000mm     | 60 mm      | 300 mm    | 32 mm | 5.13 kg     |
| WBT60X400QB<br>G  | 820055         | 3000mm     | 60 mm      | 400 mm    | 32 mm | 6.21 kg     |
| WBT60X400QE<br>G  | 820054         | 3000mm     | 60 mm      | 400 mm    | 32 mm | 6.21 kg     |
| WBT60X450QB<br>G  | 820085         | 3000mm     | 60 mm      | 450 mm    | 32 mm | 6.39 kg     |

| CatalogNumber | Article Number | Length (L) | Height (H) | Width (W) | A     | Unit Weight |
|---------------|----------------|------------|------------|-----------|-------|-------------|
| WBT60X450QEG  | 820084         | 3000mm     | 60 mm      | 450 mm    | 32 mm | 6.39 kg     |
| WBT60X500QBG  | 820065         | 3000mm     | 60 mm      | 500 mm    | 32 mm | 7.35 kg     |
| WBT60X500QEG  | 820064         | 3000mm     | 60 mm      | 500 mm    | 32 mm | 7.35 kg     |
| WBT60X600QBG  | 820079         | 3000mm     | 60 mm      | 600 mm    | 32 mm | 8.43 kg     |
| WBT60X600QEG  | 820078         | 3000mm     | 60 mm      | 600 mm    | 32 mm | 8.43 kg     |
| WBT60X60QBGG  | 820005         | 3000mm     | 60 mm      | 60 mm     | 32 mm | 2.32 kg     |


Table 2/2

| Catalog Number | Article Number | Color |
|----------------|----------------|-------|
| WBT100X100QBG  | 823015         | Black |
| WBT100X100QEG  | 823014         | Gray  |
| WBT100X150QBG  | 823025         | Black |
| WBT100X150QEG  | 823024         | Gray  |
| WBT100X200QBG  | 823035         | Black |
| WBT100X200QEG  | 823034         | Gray  |
| WBT100X300QBG  | 823045         | Black |
| WBT100X300QEG  | 823044         | Gray  |
| WBT100X400QBG  | 823055         | Black |

| Catalog Number | Article Number | Color |
|----------------|----------------|-------|
| WBT100X400QEG  | 823054         | Gray  |
| WBT100X450QBG  | 823085         | Black |
| WBT100X450QEG  | 823084         | Gray  |
| WBT100X500QBG  | 823065         | Black |
| WBT100X500QEG  | 823064         | Gray  |
| WBT100X600QBG  | 823075         | Black |
| WBT100X600QEG  | 823074         | Gray  |
| WBT60X100QBG   | 820015         | Black |
| WBT60X100QEG   | 820014         | Gray  |
| WBT60X150QBG   | 820025         | Black |
| WBT60X150QEG   | 820024         | Gray  |
| WBT60X200QBG   | 820035         | Black |
| WBT60X200QEG   | 820034         | Gray  |
| WBT60X300QBG   | 820045         | Black |
| WBT60X300QEG   | 820044         | Gray  |
| WBT60X400QBG   | 820055         | Black |
| WBT60X400QEG   | 820054         | Gray  |
| WBT60X450QBG   | 820085         | Black |

| Catalog Number | Article Number | Color |
|----------------|----------------|-------|
| WBT60X450QEG   | 820084         | Gray  |
| WBT60X500QBG   | 820065         | Black |
| WBT60X500QEG   | 820064         | Gray  |
| WBT60X600QBG   | 820079         | Black |
| WBT60X600QEG   | 820078         | Gray  |
| WBT60X60QBG    | 820005         | Black |

## DIAGRAMS



## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

#### North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

#### Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

#### Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

#### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

**CADDY**

**ERICO**

**HOFFMAN**

**ILSCO**

**SCHROFF**

**TRACHTE**

