


19" Front Panel for Thermostat With Digital Display, 1 U

19" Front Panel for Thermostat With Digital Display, 1 U



CERTIFICATIONS



FEATURES

19" Front Panel, 1 U, with cut-out for thermostat with digital display

SPECIFICATIONS

Accessory Type: Front panel

Table 1/3

| Catalog Number | Type | Mounting | EMC Shielding | Material | Front Finish | Rear Finish |
|----------------|-----------------|----------------|---------------|----------|--------------|-------------|
| 30118-267 | 19" Front Panel | Screw-on Front | No | Aluminum | Anodized | Anodized |
| 30118-315 | 19" Front Panel | Screw-on Front | No | Aluminum | Painted | Painted |
| 30118-360 | 19" Front Panel | Screw-on Front | No | Aluminum | Painted | Painted |

Table 2/3

| Catalog Number | Color Code | Rack Height | Height | Rack Width | Width | Depth |
|----------------|------------|-------------|--------|------------|-------|-------|
| 30118-267 | | 1U | 35mm | | 76mm | 3mm |
| 30118-315 | RAL 7035 | 1U | 43mm | 95HP | 483mm | 3mm |
| 30118-360 | RAL 7021 | 1U | 43mm | 95HP | 483mm | 3mm |

Table 3/3

| Catalog Number | Package Quantity | Finish | Quick Ship |
|----------------|------------------|---------------|------------|
| 30118-267 | 1 | Anodized | No |
| 30118-315 | 1 | Powder Coated | No |
| 30118-360 | 1 | Powder Coated | No |

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE