


# Interscale Mounting Plate With Built-In Fan Holder and Fans



Interscale mounting plate with built-in fan holder and fans, for desktop cases and 19" chassis. Available in different sizes and with three fan versions, with a air flow volume from 10 to 170 m3/h.

## FEATURES

Mounting plate (raised 4 mm) with integrated fan holder including fan kit for perforated case versions

Fans are simple to fit to the mounting plate using vibrationdamping fixing material

Mounting plate fixes into desktop case with 4 plastic feet or into 19" case with 4 screws

For technical data of fans, please see delivery includes

## SPECIFICATIONS

**Finish:** Aluminum-Zinc Plated

**Product Type:** Mounting Plate

Table 1/2

| Catalog Number | Width | Depth | Package Quantity | Height | Material | Product Family |
|----------------|-------|-------|------------------|--------|----------|----------------|
| 24827-154      | 221mm | 177mm | 1                | 1mm    | Steel    | Interscale     |
| 24827-155      | 221mm | 221mm | 1                | 1mm    | Steel    | Interscale     |
| 24827-175      | 310mm | 221mm | 1                | 1mm    | Steel    | Interscale     |
| 24827-195      | 399mm | 221mm | 1                | 1mm    | Steel    | Interscale     |

| CatalogNumber | Width | Depth | Package<br>Quantity | Height | Material | Product Family |
|---------------|-------|-------|---------------------|--------|----------|----------------|
| 24827-197     | 399mm | 310mm | 1                   | 1mm    | Steel    | Interscale     |
| 24827-254     |       |       | 1                   |        | Steel    | Interscale     |
| 24827-255     | 221mm | 221mm | 1                   | 1mm    | Steel    | Interscale     |
| 24827-275     | 310mm | 221mm | 1                   | 1mm    | Steel    | Interscale     |
| 24827-295     | 399mm | 221mm | 1                   | 1mm    | Steel    | Interscale     |
| 24827-297     | 399mm | 310mm | 1                   | 1mm    | Steel    | Interscale     |
| 24827-375     | 310mm | 221mm | 1                   | 1mm    | Steel    | Interscale     |
| 24827-395     | 399mm | 221mm | 1                   | 1mm    | Steel    | Interscale     |
| 24827-397     | 399mm | 310mm | 1                   | 1mm    | Steel    | Interscale     |
| 24827-105     | 444mm | 177mm | 1                   | 1mm    | Steel    | Interscale     |
| 24827-107     | 444mm | 310mm | 1                   | 1mm    | Steel    | Interscale     |
| 24827-205     |       |       | 1                   |        | Steel    |                |
| 24827-207     |       |       | 1                   |        | Steel    |                |
| 24827-305     |       |       | 1                   |        | Steel    |                |
| 24827-307     |       |       | 1                   |        | Steel    |                |

Table 2/2

| Catalog Number | Rack Width | Type           | Works With              | Quick Ship |
|----------------|------------|----------------|-------------------------|------------|
| 24827-154      |            | Mounting Plate | Small Form Factor Cases | No         |
| 24827-155      |            | Mounting Plate | Small Form Factor Cases | No         |

| Catalog Number | Rack Width | Type           | Works With              | Quick Ship |
|----------------|------------|----------------|-------------------------|------------|
| 24827-175      |            | Mounting Plate | Small Form Factor Cases | No         |
| 24827-195      |            | Mounting Plate | Small Form Factor Cases | No         |
| 24827-197      |            | Mounting Plate | Small Form Factor Cases | No         |
| 24827-254      |            | Mounting Plate |                         | No         |
| 24827-255      |            | Mounting Plate | Small Form Factor Cases | No         |
| 24827-275      |            | Mounting Plate | Small Form Factor Cases | No         |
| 24827-295      |            | Mounting Plate | Small Form Factor Cases | No         |
| 24827-297      |            | Mounting Plate | Small Form Factor Cases | No         |
| 24827-375      |            | Mounting Plate | Small Form Factor Cases | No         |
| 24827-395      |            | Mounting Plate | Small Form Factor Cases | No         |
| 24827-397      |            | Mounting Plate | Small Form Factor Cases | No         |
| 24827-105      | 19HP       | Mounting Plate | Small Form Factor Cases | No         |
| 24827-107      | 19HP       | Mounting Plate | Small Form Factor Cases | No         |
| 24827-205      |            |                |                         | No         |
| 24827-207      |            |                |                         | No         |
| 24827-305      |            |                |                         | No         |
| 24827-307      |            |                |                         | No         |

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper

installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

**North America**

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

**Europe**

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

**Asia**

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

**Middle East & India**

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**