

# Varistar CP Side Panel, Screw-Fixed

Screw assembly side panel for Varistar CP cabinet.



## FEATURES

Screw fixed, Robust and Single person mountable Side Panel

Side panel without grounding kit

## SPECIFICATIONS

**Product Type:** Cabinet/Rack Panel

Table 1/2

| Catalog Number | Rack Height | Height | Depth  | Protection Rating | Package Quantity | Color      |
|----------------|-------------|--------|--------|-------------------|------------------|------------|
| 21630-276      | 38U         | 1800mm | 1000mm | IP20              | 2                | Black Grey |
| 21630-236      | 38U         | 1800mm | 1000mm | IP55              | 2                | Black Grey |
| 21630-044      | 42U         | 2000mm | 1100mm | IP20              | 2                | Black Grey |
| 21630-242      | 42U         | 2000mm | 1100mm | IP55              | 2                | Black Grey |
| 21630-045      | 42U         | 2000mm | 1200mm | IP20              | 2                | Black Grey |
| 21630-243      | 42U         | 2000mm | 1200mm | IP55              | 2                | Black Grey |
| 21630-047      | 47U         | 2200mm | 1100mm | IP20              | 2                | Black Grey |

| CatalogNumber | Rack Height | Height | Depth  | Protection Rating | Package Quantity | Color      |
|---------------|-------------|--------|--------|-------------------|------------------|------------|
| 21630-249     | 47U         | 2200mm | 1100mm | IP55              | 2                | Black Grey |
| 21630-048     | 47U         | 2200mm | 1200mm | IP20              | 2                | Black Grey |
| 21630-250     | 47U         | 2200mm | 1200mm | IP55              | 2                | Black Grey |
| 21630-078     | 42U         | 2000mm | 1100mm | IP55              | 2                | Black Grey |
| 21630-079     | 42U         | 2000mm | 1200mm | IP55              | 2                | Black Grey |
| 21630-081     | 47U         | 2200mm | 1100mm | IP55              | 2                | Black Grey |
| 21630-082     | 47U         | 2200mm | 1200mm | IP55              | 2                | Black Grey |
| 21630-927     | 24U         | 1200mm | 900mm  | IP55              | 2                | Black Grey |
| 21630-928     | 24U         | 1200mm | 1000mm | IP55              | 2                | Black Grey |
| 21630-929     | 29U         | 1400mm | 900mm  | IP55              | 2                | Black Grey |
| 21630-930     | 29U         | 1400mm | 1000mm | IP55              | 2                | Black Grey |
| 21630-931     | 33U         | 1600mm | 900mm  | IP55              | 2                | Black Grey |
| 21630-932     | 33U         | 1600mm | 1000mm | IP55              | 2                | Black Grey |
| 21630-933     | 38U         | 1800mm | 900mm  | IP55              | 2                | Black Grey |
| 21630-934     | 38U         | 1800mm | 1000mm | IP55              | 2                | Black Grey |
| 21630-261     | 24U         | 1200mm | 600mm  | IP20              | 2                | Black Grey |
| 21630-221     | 24U         | 1200mm | 600mm  | IP55              | 2                | Black Grey |
| 21630-262     | 24U         | 1200mm | 800mm  | IP20              | 2                | Black Grey |

| CatalogNumber | Rack Height | Height | Depth | Protection Rating | Package Quantity | Color      |
|---------------|-------------|--------|-------|-------------------|------------------|------------|
| 21630-222     | 24U         | 1200mm | 800mm | IP55              | 2                | Black Grey |
| 21630-265     | 29U         | 1400mm | 600mm | IP20              | 2                | Black Grey |
| 21630-225     | 29U         | 1400mm | 600mm | IP55              | 2                | Black Grey |
| 21630-266     | 29U         | 1400mm | 800mm | IP20              | 2                | Black Grey |
| 21630-226     | 29U         | 1400mm | 800mm | IP55              | 2                | Black Grey |
| 21630-269     | 33U         | 1600mm | 600mm | IP20              | 2                | Black Grey |
| 21630-229     | 33U         | 1600mm | 600mm | IP55              | 2                | Black Grey |
| 21630-270     | 33U         | 1600mm | 800mm | IP20              | 2                | Black Grey |
| 21630-230     | 33U         | 1600mm | 800mm | IP55              | 2                | Black Grey |
| 21630-273     | 38U         | 1800mm | 600mm | IP20              | 2                | Black Grey |
| 21630-233     | 38U         | 1800mm | 600mm | IP55              | 2                | Black Grey |
| 21630-274     | 38U         | 1800mm | 800mm | IP20              | 2                | Black Grey |
| 21630-234     | 38U         | 1800mm | 800mm | IP55              | 2                | Black Grey |
| 21630-277     | 42U         | 2000mm | 300mm | IP20              | 2                | Black Grey |
| 21630-237     | 42U         | 2000mm | 300mm | IP55              | 2                | Black Grey |
| 21630-278     | 42U         | 2000mm | 600mm | IP20              | 2                | Black Grey |
| 21630-238     | 42U         | 2000mm | 600mm | IP55              | 2                | Black Grey |
| 21630-279     | 42U         | 2000mm | 800mm | IP20              | 2                | Black Grey |

| CatalogNumber | Rack Height | Height | Depth  | Protection Rating | Package Quantity | Color      |
|---------------|-------------|--------|--------|-------------------|------------------|------------|
| 21630-239     | 42U         | 2000mm | 800mm  | IP55              | 2                | Black Grey |
| 21630-280     | 42U         | 2000mm | 900mm  | IP20              | 2                | Black Grey |
| 21630-240     | 42U         | 2000mm | 900mm  | IP55              | 2                | Black Grey |
| 21630-043     | 42U         | 2000mm | 1000mm | IP20              | 2                | Black Grey |
| 21630-241     | 42U         | 2000mm | 1000mm | IP55              | 2                | Black Grey |
| 21630-281     | 47U         | 2200mm | 300mm  | IP20              | 2                | Black Grey |
| 21630-244     | 47U         | 2200mm | 300mm  | IP55              | 2                | Black Grey |
| 21630-282     | 47U         | 2200mm | 600mm  | IP20              | 2                | Black Grey |
| 21630-245     | 47U         | 2200mm | 600mm  | IP55              | 2                | Black Grey |
| 21630-283     | 47U         | 2200mm | 800mm  | IP20              | 2                | Black Grey |
| 21630-246     | 47U         | 2200mm | 800mm  | IP55              | 2                | Black Grey |
| 21630-284     | 47U         | 2200mm | 900mm  | IP20              | 2                | Black Grey |
| 21630-247     | 47U         | 2200mm | 900mm  | IP55              | 2                | Black Grey |
| 21630-046     | 47U         | 2200mm | 1000mm | IP20              | 2                | Black Grey |
| 21630-248     | 47U         | 2200mm | 1000mm | IP55              | 2                | Black Grey |
| 21630-465     | 24U         | 1200mm | 600mm  | IP55              | 2                | Black Grey |
| 21630-466     | 24U         | 1200mm | 800mm  | IP55              | 2                | Black Grey |
| 21630-467     | 29U         | 1400mm | 600mm  | IP55              | 2                | Black Grey |

| CatalogNumber | Rack Height | Height | Depth  | Protection Rating | Package Quantity | Color      |
|---------------|-------------|--------|--------|-------------------|------------------|------------|
| 21630-468     | 29U         | 1400mm | 800mm  | IP55              | 2                | Black Grey |
| 21630-469     | 33U         | 1600mm | 600mm  | IP55              | 2                | Black Grey |
| 21630-470     | 33U         | 1600mm | 800mm  | IP55              | 2                | Black Grey |
| 21630-471     | 38U         | 1800mm | 600mm  | IP55              | 2                | Black Grey |
| 21630-472     | 38U         | 1800mm | 800mm  | IP55              | 2                | Black Grey |
| 21630-473     | 42U         | 2000mm | 300mm  | IP55              | 2                | Black Grey |
| 21630-474     | 42U         | 2000mm | 600mm  | IP55              | 2                | Black Grey |
| 21630-475     | 42U         | 2000mm | 800mm  | IP55              | 2                | Black Grey |
| 21630-476     | 42U         | 2000mm | 900mm  | IP55              | 2                | Black Grey |
| 21630-077     | 42U         | 2000mm | 1000mm | IP55              | 2                | Black Grey |
| 21630-477     | 47U         | 2200mm | 300mm  | IP55              | 2                | Black Grey |
| 21630-478     | 47U         | 2200mm | 600mm  | IP55              | 2                | Black Grey |
| 21630-479     | 47U         | 2200mm | 800mm  | IP55              | 2                | Black Grey |
| 21630-480     | 47U         | 2200mm | 900mm  | IP55              | 2                | Black Grey |
| 21630-080     | 47U         | 2200mm | 1000mm | IP55              | 2                | Black Grey |
| 21630-049     | 52U         | 2450mm | 1000mm | IP20              | 2                | Black Grey |
| 21630-051     | 52U         | 2450mm | 1200mm | IP20              | 2                | Black Grey |
| 21630-050     | 52U         | 2450mm | 1100mm | IP20              | 2                | Black Grey |

| CatalogNumber | Rack Height | Height | Depth  | Protection Rating | Package Quantity | Color      |
|---------------|-------------|--------|--------|-------------------|------------------|------------|
| 21630-263     | 24U         | 1200mm | 900mm  | IP20              | 2                | Black Grey |
| 21630-223     | 24U         | 1200mm | 900mm  | IP55              | 2                | Black Grey |
| 21630-224     | 24U         | 1200mm | 1000mm | IP55              | 2                | Black Grey |
| 21630-264     | 24U         | 1200mm | 1000mm | IP20              | 2                | Black Grey |
| 21630-267     | 29U         | 1400mm | 900mm  | IP20              | 2                | Black Grey |
| 21630-227     | 29U         | 1400mm | 900mm  | IP55              | 2                | Black Grey |
| 21630-268     | 29U         | 1400mm | 1000mm | IP20              | 2                | Black Grey |
| 21630-228     | 29U         | 1400mm | 1000mm | IP55              | 2                | Black Grey |
| 21630-271     | 33U         | 1600mm | 900mm  | IP20              | 2                | Black Grey |
| 21630-231     | 33U         | 1600mm | 900mm  | IP55              | 2                | Black Grey |
| 21630-272     | 33U         | 1600mm | 1000mm | IP20              | 2                | Black Grey |
| 21630-232     | 33U         | 1600mm | 1000mm | IP55              | 2                | Black Grey |
| 21630-275     | 38U         | 1800mm | 900mm  | IP20              | 2                | Black Grey |
| 21630-235     | 38U         | 1800mm | 900mm  | IP55              | 2                | Black Grey |

Table 2/2

| Catalog Number | Color Code | Finish        | Material | Type                    | Quick Ship |
|----------------|------------|---------------|----------|-------------------------|------------|
| 21630-276      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed | No         |
| 21630-236      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed | No         |
| 21630-044      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed | No         |

| Catalog Number | Color Code | Finish        | Material | Type                    | Quick Ship |
|----------------|------------|---------------|----------|-------------------------|------------|
| 21630-242      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed | No         |
| 21630-045      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed | No         |
| 21630-243      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed | No         |
| 21630-047      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed | No         |
| 21630-249      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed | No         |
| 21630-048      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed | No         |
| 21630-250      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed | No         |
| 21630-078      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed | No         |
| 21630-079      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed | No         |
| 21630-081      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed | No         |
| 21630-082      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed | No         |
| 21630-927      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed | No         |
| 21630-928      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed | No         |
| 21630-929      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed | No         |
| 21630-930      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed | No         |
| 21630-931      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed | No         |
| 21630-932      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed | No         |
| 21630-933      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed | No         |

| Catalog Number | Color Code | Finish        | Material | Type                    | Quick Ship |
|----------------|------------|---------------|----------|-------------------------|------------|
| 21630-934      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed | No         |
| 21630-261      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed | No         |
| 21630-221      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed | No         |
| 21630-262      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed | No         |
| 21630-222      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed | No         |
| 21630-265      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed | No         |
| 21630-225      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed | No         |
| 21630-266      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed | No         |
| 21630-226      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed | No         |
| 21630-269      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed | No         |
| 21630-229      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed | No         |
| 21630-270      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed | No         |
| 21630-230      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed | No         |
| 21630-273      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed | No         |
| 21630-233      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed | No         |
| 21630-274      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed | No         |
| 21630-234      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed | No         |
| 21630-277      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed | No         |

| Catalog Number | Color Code | Finish        | Material | Type                    | Quick Ship |
|----------------|------------|---------------|----------|-------------------------|------------|
| 21630-237      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed | No         |
| 21630-278      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed | No         |
| 21630-238      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed | No         |
| 21630-279      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed | No         |
| 21630-239      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed | No         |
| 21630-280      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed | No         |
| 21630-240      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed | No         |
| 21630-043      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed | No         |
| 21630-241      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed | No         |
| 21630-281      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed | No         |
| 21630-244      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed | No         |
| 21630-282      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed | No         |
| 21630-245      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed | No         |
| 21630-283      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed | No         |
| 21630-246      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed | No         |
| 21630-284      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed | No         |
| 21630-247      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed | No         |
| 21630-046      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed | No         |

| Catalog Number | Color Code | Finish        | Material | Type                    | Quick Ship |
|----------------|------------|---------------|----------|-------------------------|------------|
| 21630-248      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed | No         |
| 21630-465      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed | No         |
| 21630-466      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed | No         |
| 21630-467      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed | No         |
| 21630-468      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed | No         |
| 21630-469      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed | No         |
| 21630-470      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed | No         |
| 21630-471      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed | No         |
| 21630-472      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed | No         |
| 21630-473      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed | No         |
| 21630-474      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed | No         |
| 21630-475      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed | No         |
| 21630-476      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed | No         |
| 21630-077      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed | No         |
| 21630-477      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed | No         |
| 21630-478      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed | No         |
| 21630-479      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed | No         |
| 21630-480      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed | No         |

| Catalog Number | Color Code | Finish        | Material | Type                    | Quick Ship |
|----------------|------------|---------------|----------|-------------------------|------------|
| 21630-080      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed | No         |
| 21630-049      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed | No         |
| 21630-051      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed | No         |
| 21630-050      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed | No         |
| 21630-263      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed | No         |
| 21630-223      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed | No         |
| 21630-224      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed | No         |
| 21630-264      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed | No         |
| 21630-267      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed | No         |
| 21630-227      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed | No         |
| 21630-268      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed | No         |
| 21630-228      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed | No         |
| 21630-271      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed | No         |
| 21630-231      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed | No         |
| 21630-272      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed | No         |
| 21630-232      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed | No         |
| 21630-275      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed | No         |
| 21630-235      | RAL 7021   | Powder Coated | Steel    | Side Panel, Screw Fixed | No         |

ADDITIONAL PRODUCT DETAILS

Please purchase the grounding kit separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Our powerful portfolio of brands:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE