

# Z-Rail for Connector, EN 60603-2, DIN 41612

## Power Utilities



Z-rail for connector in accordance with EN 60603-2 (DIN 41612).

## CERTIFICATIONS



## FEATURES

Z-rails are bolted to the subrack for connector mounting (rear horizontal rail type ST, threaded insert inserted)

For connectors to EN 60603-2 (DIN 41612)

Aluminum extrusion, anodized

## SPECIFICATIONS

Table 1/2

| Catalog Number | Rack Width | Package Quantity | Length    | Product Family                                                                | Product Type | Works With         |
|----------------|------------|------------------|-----------|-------------------------------------------------------------------------------|--------------|--------------------|
| 30822-089      | 84 HP      | 1                | 426.72 mm | EuropacPRO,<br>RatiopacPRO,<br>RatiopacPRO<br>AIR,<br>CompacPRO,<br>PropacPRO | Z-Rail       | Subracks,<br>Cases |

| CatalogNumber | Rack Width | Package Quantity | Length    | Product Family                                                 | Product Type | Works With      |
|---------------|------------|------------------|-----------|----------------------------------------------------------------|--------------|-----------------|
| 30822-033     | 28 HP      | 1                | 142.24 mm | EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO | Z-Rail       | Subracks, Cases |
| 30822-047     | 42 HP      | 1                | 213.36 mm | EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO | Z-Rail       | Subracks, Cases |
| 30822-065     | 60 HP      | 1                | 304.8 mm  | EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO | Z-Rail       | Subracks, Cases |
| 30822-166     | 4 HP       | 1                | 20.32 mm  | EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO | Z-Rail       | Subracks, Cases |
| 30822-170     | 8 HP       | 1                | 40.64 mm  | EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO | Z-Rail       | Subracks, Cases |

Table 2/2

| Catalog Number | Certifications |
|----------------|----------------|
| 30822-089      | RoHS           |
| 30822-033      | RoHS           |
| 30822-047      | RoHS           |
| 30822-065      | RoHS           |
| 30822-166      | RoHS           |

| Catalog Number | Certifications |
|----------------|----------------|
| 30822-170      |                |

ADDITIONAL PRODUCT DETAILS

For attaching the z-rail to the horizontal rail a threaded insert and Torx panhead screw are required; please order these separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE