

# Locking System For Lift Handles, LHC



The locking inserts and cylinders can be mounted independently in the lift handle, which means many combinations can be created. This reduces the number of handles to be stocked.

## FEATURES

---

Description: Profile half cylinder locks. To be used in the lift handles LHC.

Pack quantity: 1 piece.

## SPECIFICATIONS

**Width:** 23mm  
**Height:** 37mm  
**Depth:** 41mm  
**Color:** Black Gray  
**Finish:** Smooth Matte

Table 1/1

Catalog Number	Key Type	Key Code	Cylinder Type	Enclosure Material	Product Family	Material
LHC526	Triangle 7 mm		Round	Mild Steel	Free-Standing	Plastic, Plastic
LHC533	Cylinder N°E1 (VW), key excluded		Half	Mild Steel	Free-Standing	Plastic, Plastic
LHC521	Ronis	C21323	Half	Mild Steel	Free-Standing	Plastic, Plastic
LHC522	Ronis	C21323	Round	Mild Steel	Free-Standing	Plastic, Plastic
LHC523	Square 7 mm		Round	Mild Steel	Free-Standing	Plastic, Plastic
LHC524	Square 8 mm		Round	Mild Steel	Free-Standing	Plastic, Plastic
LHC527	Triangle 8 mm		Round	Mild Steel	Free-Standing	Plastic, Plastic
LHC528	Double-bit 3 mm		Round	Mild Steel	Free-Standing	Plastic, Plastic
LHC529	Double-bit 5 mm		Round	Mild Steel	Free-Standing	Plastic, Plastic
LHC530	Daimler Benz		Round	Mild Steel	Free-Standing	Plastic, Plastic
LHC534	Adapter for other profile half cylinders (DIN18252)		Half	Mild Steel	Free-Standing	Plastic, Plastic
LHC535	Adapter for ASSA ABLOY and Trioing cylinders		Half	Mild Steel	Free-Standing	Plastic, Plastic
LHC536	Push button only		Round	Mild Steel	Free-Standing	Plastic, Plastic
LHC5212132E	Ronis	2132E	Half	Mild Steel	Free-Standing	Plastic, Plastic

Catalog Number	Key Type	Key Code	Cylinder Type	EnclosureMaterial	Product Family	Material
LHC5213121E	Ronis	3121E	Half	Mild Steel	Free-Standing	Plastic, Plastic
LHC531	Lock insert slotted 2x4 mm		Round	Mild Steel	Free-Standing	Mild Steel

### ADDITIONAL PRODUCT DETAILS

\* Other key numbers available on request. \*\* Key numbers 333, 1333, EK333 and GX130 are equal. \*\*\* Order separate key LSMK for Square 8 mm and Triangle 8 mm.

### WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE