

# Varistar CP Base/Plinth

## Power Utilities

A plinth allows functional storage of excess cable assemblies and protects the bottom part of the cabinet against rodents.

### FEATURES

2 support profiles, for front and rear

Static load-carrying capacity 1000 kg

### SPECIFICATIONS

Table 1/2

| Catalog Number | Height | Width  | Color      | Color Code | Depth  | Finish        |
|----------------|--------|--------|------------|------------|--------|---------------|
| 24630-034      | 100 mm | 600 mm | Black Grey | RAL 7021   | 600 mm | Powder Coated |
| 24630-035      | 100 mm | 800 mm | Black Grey | RAL 7021   |        | Powder Coated |
| 24630-064      | 100 mm | 600 mm | Black Grey | RAL 7021   |        | Powder Coated |
| 24630-065      | 100 mm | 800 mm | Black Grey | RAL 7021   |        | Powder Coated |
| 24630-036      | 200 mm | 600 mm | Black Grey | RAL 7021   |        | Powder Coated |
| 24630-037      | 200 mm | 800 mm | Black Grey | RAL 7021   |        | Powder Coated |
| 24630-066      | 200 mm | 600 mm | Black Grey | RAL 7021   |        | Powder Coated |
| 24630-067      | 200 mm | 800 mm | Black Grey | RAL 7021   |        | Powder Coated |

Table 2/2

| Catalog Number | Material | Product Type | Type |
|----------------|----------|--------------|------|
|----------------|----------|--------------|------|

|           |       |                   |             |
|-----------|-------|-------------------|-------------|
| 24630-034 | Steel | Cabinet/Rack Base | Base Plinth |
| 24630-035 | Steel | Cabinet/Rack Base | Base Plinth |
| 24630-064 | Steel | Cabinet/Rack Base | Base Plinth |
| 24630-065 | Steel | Cabinet/Rack Base | Base Plinth |
| 24630-036 | Steel | Cabinet/Rack Base | Base Plinth |
| 24630-037 | Steel | Cabinet/Rack Base | Base Plinth |
| 24630-066 | Steel | Cabinet/Rack Base | Base Plinth |
| 24630-067 | Steel | Cabinet/Rack Base | Base Plinth |

## ADDITIONAL PRODUCT DETAILS

---

Please order side trims separately.

Cannot be used in conjunction with castors

## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**