


# RatiopacPRO 19" Bracket Kit, Retrofitting



For conversion of Ratiopac cases with cover strip or front handle. The retrofitting of the brackets can be done without disassembly of the case.

## CERTIFICATIONS



## FEATURES

For conversion of cases with cover strip or front handle

## SPECIFICATIONS

**Material:** Aluminum  
**Product Type:** Bracket  
**Color Code:** RAL 7016

Table 1/2

| Catalog Number | Rack Height | Package Quantity | Color | Finish | Product Family | Works With |
|----------------|-------------|------------------|-------|--------|----------------|------------|
|----------------|-------------|------------------|-------|--------|----------------|------------|

|           |    |   |            |               |                                                                |                              |
|-----------|----|---|------------|---------------|----------------------------------------------------------------|------------------------------|
| 24571-994 | 2U | 2 | Light Grey | Powder Coated | RatiopacPRO,<br>RatiopacPRO<br>AIR,<br>PropacPRO,<br>CompacPRO | Cases,<br>RatiopacPRO        |
| 24571-295 | 3U | 2 | Light Grey | Powder Coated | RatiopacPRO,<br>RatiopacPRO<br>AIR,<br>PropacPRO,<br>CompacPRO | Cases,<br>RatiopacPRO        |
| 24571-296 | 4U | 2 | Light Grey | Powder Coated | RatiopacPRO,<br>RatiopacPRO<br>AIR,<br>PropacPRO,<br>CompacPRO | Cases,<br>RatiopacPRO        |
| 24571-298 | 4U | 2 | Light Grey | Powder Coated | RatiopacPRO<br>AIR                                             | Cases,<br>RatiopacPRO<br>AIR |
| 24571-992 | 5U | 2 | Light Grey | Powder Coated | RatiopacPRO,<br>RatiopacPRO<br>AIR,<br>PropacPRO,<br>CompacPRO | Cases,<br>RatiopacPRO        |
| 24571-299 | 5U | 2 | Light Grey | Powder Coated | RatiopacPRO<br>AIR                                             | Cases,<br>RatiopacPRO<br>AIR |
| 24571-297 | 6U | 2 | Light Grey | Powder Coated | RatiopacPRO,<br>RatiopacPRO<br>AIR,<br>PropacPRO,<br>CompacPRO | Cases,<br>RatiopacPRO        |
| 24571-300 | 7U | 2 | Light Grey | Powder Coated | RatiopacPRO<br>AIR                                             | Cases,<br>RatiopacPRO<br>AIR |

Table 2/2

| Catalog Number | Quick Ship |
|----------------|------------|
| 24571-994      | No         |
| 24571-295      | No         |
| 24571-296      | No         |
| 24571-298      | No         |

| Catalog Number | Quick Ship |
|----------------|------------|
| 24571-992      | No         |
| 24571-299      | No         |
| 24571-297      | No         |
| 24571-300      | No         |

## ADDITIONAL PRODUCT DETAILS

No slide rails may be used when fitting into cabinets or 19" cases.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**