


Sleeves for M2.5



Sleeve guides the collar screw when fastening the front panel.

CERTIFICATIONS



FEATURES

Sleeve guides the collar screw when fastening the front panel

Sleeve is inserted into the elongated hole of the front panel

SPECIFICATIONS

Works With: Front Panels

Product Type: Sleeve

Table 1/2

Catalog Number	Material	Finish	Color	Package Quantity	Color Code	Depth (D)
21100-659	Brass	Nickel Plated		10		
21100-661	Stainless Steel			10		
21100-662	Stainless Steel			100		4.4mm

CatalogNumber	Material	Finish	Color	Package Quantity	Color Code	Depth (D)
21100-660	Brass	Nickel Plated		100		4.4mm
21100-886	Brass	Organic Top Coat		100		4.4mm
21100-464	Polyamide 6		Pebble Grey	100	RAL 7032	6.9mm
21100-591	Polyamide 6		Jet Black	100	RAL 9005	6.9mm
21100-885	Brass			10		


Table 2/2

Catalog Number	Height (H)	Width (W)	Flammability Rating	Quick Ship
21100-659				No
21100-661				No
21100-662	6mm	8mm		No
21100-660	6mm	8mm		No
21100-886	6mm	8mm		No
21100-464	6mm	6.8mm	UL® 94V-2	No
21100-591	6mm	6.8mm	UL® 94V-2	No
21100-885				No

ADDITIONAL PRODUCT DETAILS

Metal sleeves on the partial front panels must be pressed in.

All sleeves can be used for front panel > 2 HP.



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE